




LOC	DIST			REVISIONS				
AF	50	P	F	ZONE	LTR	DESCRIPTION	DATE	APPD
					E	REVISE PER ECN 0G1A-0180-99	12JUL99	SW/KR

- 1 CONTINUOUS STRIP ON REELS WITH TERMINALS LOCATED ON 5.59 ± 0.08 [$.220 \pm .003$] CENTERS.
- 2 SLOT ACCEPTS $0.25-0.36\text{mm}$ [#30-#27] AWG COPPER MAGNET WIRE. 2 WIRES OF THE SAME SIZE PER SLOT.
- 3 POKE-IN ACCEPTS A $0.50-0.90\text{mm}^2$ [#20-#18] AWG SOLID OR FUSED STRANDED LEAD WIRE.
- 4 TERMINAL IS DESIGNED FOR A 1.78 [$.070$] TO 2.79 [$.110$] ANVIL HEIGHT.



					63636-1	
					PART NO	
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON : 2 PLC DEC ± 0.25 [0.010] 3 PLC DEC ± - ANGLES ± - MATERIAL 4M BRASS		DR 1/9/92 MICHAEL S. FEHER		AMP AMP Incorporated Harrisburg, PA 17105-3608		
		CHK 1/14/92 JEFF R. RUTH				
		APPD 1/14/92 NELSON E. NEFF				
		APPD 1/14/92 TERRY L. SHUTTER				
		PRODUCT SPEC 108-2012		NAME TERMINAL, POKE-IN, 300 SERIES MAG-MATE™		
FINISH 0.002032 [0.00080] MIN TIN		APPLICATION SPEC 114-2046		SIZE C		CAGE CODE 00779
		WEIGHT _		DRAWING NO 63636		
				SHEET 1 OF 1		
		4		SCALE 10:1		

METRIC