

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.


REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	10/11/10	D.GRIFFIN

D

C

B

A




MOLDED GRAY
PVC HOOD
(PANTONE 424C)

"J1"
DB37 FEMALE
CONNECTOR
WITH BACK
HEX NUTS

2X #4-40 UNC-2A
HEX JACKSCREW

PIN 1




2X #4-40 UNC-2A

"P1"
DB37 MALE
CONNECTOR
WITH BACK
HEX NUTS

2X .149±.014
[3.8±0.35]


PIN 1




- NOTES:**
1. ADAPTER SHALL BE TESTED FOR CONTINUITY.
 2. ADAPTER SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.
 3. PRODUCT SHIPPED IN STANDARD HARDWARE CONFIGURATION SHOWN ABOVE AND IN EXPLODED VIEW.
 4. ADAPTER IS WIRED STRAIGHT THROUGH FROM PIN TO LIKE-NUMBERED PIN.

HARDWARE CONFIGURATIONS


STANDARD HARDWARE CONFIGURATION



ALTERNATE HARDWARE CONFIGURATION



RoHS Compliant ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0%		APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005		DRAWN BY D.FRISIELLO	6/2/10		
PROJECTION 		CHECKED BY C.BRAN	6/2/10	CATEGORY DATA	
COLOR VARIATIONS MAY OCCUR		APPROVED BY S.SMITH	6/2/10	PRODUCT DESCRIPTION ADPT,DB37M/F RA ORIENTATION 2	
REF		SIZE A	FSCM NO. 43321	DWG. NO. DG9037MF2	REV. A
SCALE: NONE		CAD FILE: DG9037MF2.SLDDRW		SHEET 1 OF 1	