

PANEL MOUNT INDICATOR, NON-RELAMPABLE

NEON TECHNOLOGY

MOUNTING HOLE, Ø 0.380"

PART NO.	LENS COLOR	VOLTAGE	CURRENT [mA]	RATED LIFE HOURS
NEON 115VAC SERIES				
WL-6010M1	RED	105-125VAC	1.5mA	25,000
WL-6010M3	AMBER	105-125VAC	1.5mA	25,000
WL-6012M5	GREEN	105-125VAC	1.5mA	25,000
NEON 230VAC SERIES				
WL-6011M1	RED	208-250VAC	1.5mA	25,000
WL-6011M3	AMBER	208-250VAC	1.5mA	25,000
WL-6013M5	GREEN	208-250VAC	1.5mA	25,000

NOTES


1. Recommended panel thickness
0.030" to 0.250"
2. 6" leads with 1/2" strip are standard
3. Storage temperature
 T_{STG} : -25°C - +100°C
4. Ambient temperature
 T_A : -20°C - +100°C
5. Voltage tolerance
 V_{OP} : $\pm 10\%$
6. Body material
Nylon, white
7. Lens material
Polycarbonate
8. Bezel material
Stainless steel
9. Wire gauge
18 AWG
10. Gaskets
Buna-N
11. Mounting hardware (nut, lock washer, and gasket) included

CERTIFICATIONS

UL (E340667), RoHS



DIMENSIONAL CHARACTERISTICS



unless otherwise specified, all dimensions are in inches



OPTIONS

Additional options and lens styles available. Please contact Wamco for more information.

