

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0022012187](#)
Status: **Active**
Overview: [KK®](#)
Description: 2.54mm (.100") Pitch KK® Crimp Terminal Housing, Friction Ramp, 18 Circuits, Use with 2759|6459|41572

Documents:

3D Model	Product Specification PS-10-07 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	Crimp Housings
Series	2695
Overview	KK®
Product Name	KK®

Physical

Circuits (maximum)	18
Color - Resin	Natural (White)
Flammability	94V-0
Gender	Female
Glow-Wire Compliant	No
Lock to Mating Part	Yes
Material - Resin	Nylon
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface (in)	0.100 In
Pitch - Mating Interface (mm)	2.54 mm
Stackable	No
Temperature Range - Operating	0°C to +75°C

Electrical


CSA	LR19980
UL	E29179

Material Info

Old Part Number	2695-18R
-----------------	----------

Reference - Drawing Numbers

Product Specification	PS-10-07
Sales Drawing	SD-2695



Series image - Reference only

EU RoHS

**ELV and RoHS
Compliant**
**REACH SVHC
Contains SVHC: No
Halogen-Free
Status**

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

[2695](#) Series

Mates With

2.54mm (.100") Pitch KK® Crimp Terminal
Housing, Friction Ramp, 18 Circuits, Use
with 2759|6459|41572

Use With

KK® Crimp Terminal Housing [2695](#) , [6471](#) ,
[7880](#)