


Conformal Coated RF Chokes

Special Features

- High Q & self resonant frequency
- Low DCR
- Ferrite bobbin core
- Epoxy coated to protect winding form harsh environments
- Low cost
- Color bands identification (Per EIA Standard)
- Dielectric strength 500Vrms
- Operating temperature -55 - +105°C

Notes

- * Current to cause 35°C maximum temperature rise



Dimensions: Inches

78F Series						
Part Number	L (μH) ±20%	Q Min.	Test Freq. (MHz)	SRF (MHz) Min.	DCR Ω Max.	I, DC* (mA)
78FR033M	0.033	50	50	400	0.02	500
78FR10M	0.10	40	25	400	0.06	500
78FR12M	0.12	40	25	400	0.06	500
78FR15M	0.15	40	25	400	0.07	500
78FR18M	0.18	40	25	400	0.08	450
±10%						
78FR22K	0.22	40	25	380	0.08	1025
78FR27K	0.27	40	25	360	0.08	950
78FR33K	0.33	40	25	350	0.08	815
78FR39K	0.39	40	25	320	0.09	700
78FR47K	0.47	40	25	330	0.10	650
78FR56K	0.56	40	25	280	0.11	545
78FR68K	0.68	40	25	250	0.12	495
78FR82K	0.82	40	25	200	0.12	415
78F1R0K	1.0	40	25	180	0.15	385
78F1R2K	1.2	40	7.9	165	0.18	590
78F1R5K	1.5	45	7.9	150	0.20	535
78F1R8K	1.8	50	7.9	125	0.25	455
78F2R2K	2.2	50	7.9	110	0.28	395
78F2R7K	2.7	50	7.9	95	0.30	355
±5%						
78F3R3J	3.3	50	7.9	70	0.34	270
78F3R9J	3.9	45	7.9	65	0.32	250
78F4R7J	4.7	45	7.9	50	0.35	230
78F5R6J	5.6	45	7.9	40	0.40	185
78F6R8J	6.8	40	7.9	30	0.45	175
78F8R2J	8.2	40	7.9	28	0.55	155
78F100J	10	40	7.9	22	0.72	130
78F120J	12	45	2.5	20	0.80	155
78F150J	15	50	2.5	16	0.88	150
78F180J	18	50	2.5	15	1.00	145
78F220J	22	50	2.5	13	1.20	140
78F270J	27	50	2.5	11	1.35	135
78F330J	33	50	2.5	10	1.50	195
78F390J	39	50	2.5	9.5	1.70	185
78F470J	47	60	2.5	8.5	2.30	167
78F560J	56	60	2.5	7.5	2.60	150
78F680J	68	60	2.5	6.5	2.90	137
78F820J	82	60	2.5	6.0	3.20	132
78F101J	100	60	2.5	5.5	3.50	125
78F121J	120	60	0.79	5.4	3.80	100
78F151J	150	60	0.79	4.7	4.40	90
78F181J	180	60	0.79	4.3	5.00	84
78F221J	220	60	0.79	4.0	5.70	76
78F271J	270	60	0.79	3.7	6.50	70
78F331J	330	60	0.79	3.4	9.50	65
78F391J	390	60	0.79	2.8	10.5	60
78F471J	470	60	0.79	2.5	11.6	53
78F561J	560	60	0.79	2.3	13.0	51
78F681J	680	60	0.79	2.0	18.0	45
78F821J	820	60	0.79	1.5	23.0	43
78F102J	1000	60	0.79	1.2	26.0	41

Also available as RoHS compliant.

J.W. Miller
M A G N E T I C S

306 E. Alondra Blvd. Gardena, CA 90247-1059 • Phone (310) 515-1720 • FAX (310) 515-1962

www.jwmiller.com