

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0530202610
Status: Obsolete
Description: 1.50mm (.059") Pitch Header, Dual Row, Right Angle, 26 Circuits

Documents:

General

Product Family	PCB Headers
Series	53020
Application	Board-to-Board, Signal
Obsolete Date	2003/06/01
Product Name	N/A


Physical

Breakaway	No
Circuits (Loaded)	26
Circuits (maximum)	26
Glow-Wire Compliant	No
Lock to Mating Part	None
Number of Rows	2
Orientation	Right Angle
PC Tail Length	2.30mm (.091")
PCB Locator	No
PCB Retention	Yes
PCB Thickness - Recommended	0.80mm (.031")
Packaging Type	Tray
Pitch - Mating Interface	1.50mm (.059")
Pitch - Termination Interface	1.50mm (.059")
Polarized to PCB	No
Shrouded	Partial
Stackable	No
Temperature Range - Operating	-40°C to +105°C
Termination Interface: Style	Through Hole, Through Hole - Kinked Pin

Electrical

Current - Maximum per Contact	1A
Voltage - Maximum	125V

Material Info



EU RoHS

ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Not Low-Halogen

China RoHS



Need more information on product
environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series
53020Series

Mates With
52022