

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
DF	X5	A		RELEASED PER ECO-05-001646	06-05	AA

- 1


TOLERANCE OF LEAD LENGTH:
UP TO 24 INCHES [609.6] = ±.12 [±3.0]
24 INCHES [609.6] & UP = ±1%
- 2

MARKED PER MIL-STD-130.
- 3

TO MATE WITH AMP LGH-1/2
RECEPTACLE WITH .53 [13.4] BARREL DEPTH.
- 4

INSULATION CUT TO LENGTH 'B' BUT NOT REMOVED.
- 5

OPERATING VOLTAGE: 10 KVDC AT 0 TO 70,000 FEET, -55°C TO 125°C.



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A.H.ANDERSON 09-JUN-05	Tyco Electronics Corporation Harriaburg, Pa 17105-3608	
DIMENSIONS: INCHES		CHK D. EABY 09-JUN-05	NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± .02 [0.5] 3 PLC ± - 4 PLC ± - ANGLES ± -		APVD D. EABY 09-JUN-05	LEAD ASS'Y SGL END LGH-1/2	
MATERIAL SEE CALLOUTS		FINISH SEE CALLOUTS	WEIGHT -	RESTRICTED TO -
CUSTOMER DRAWING			SCALE 4:1	SHEET 1 OF 1