

SPECIFICATIONS

Current Rating:

3 Amp

Insulator Resistance:

5000 Megohms Min.

Contact Resistance:

20 m ohms Max.

Dielectric withstanding:

AC 500V/minute

Operating Temperature:

Brass ~ +105°C

Contact Material:

Insulator Material:

High Temperature Thermoplastic

High Glass Fibre UL94V-0

Finish: Black

Gold,Tin or Duplex plated

Standard: Gold flash all over

Duplex plated:

Gold plated on contact area

Tin on solder area

RoHS Compliant

Ordering information: 

22P8562-XXS10X-XXX-X

Number of Contact 04~80

Color

Contact Plating

01 Normal

10 10μ"

⋮




B PBT

N Nylon-6T

G Gold Plated

T Tin Plated

H Duplex plated



RECOMMENDED P. C. B. LAYOUT

Cir- cuits	Dimension mm	
	L1	L2
2X2	2.54	5.08
2X3	5.08	7.62
2X4	7.62	10.16
2X5	10.16	12.70
2X6	12.70	15.24
2X7	15.24	17.78
2X8	17.78	20.32
2X9	20.32	22.86
2X10	22.86	25.40
2X11	25.40	27.94
2X12	27.94	30.48
2X13	30.48	33.02
2X14	33.02	35.56
2X15	35.56	38.10
2X16	38.10	40.64
2X17	40.64	43.18
2X18	43.18	45.72
2X19	45.72	48.26
2X20	48.26	50.80
2X21	50.80	53.34
2X22	53.34	55.88
2X23	55.88	58.42
2X24	58.42	60.96
2X25	60.96	63.50
2X26	63.50	66.04
2X27	66.04	68.58
2X28	68.58	71.12
2X29	71.12	73.66
2X30	73.66	76.20
2X31	76.20	78.74
2X32	78.74	81.28
2X33	81.28	83.82
2X34	83.82	86.36
2X35	86.36	88.90
2X36	88.90	91.44
2X37	91.44	93.98
2X38	93.98	96.52
2X39	96.52	99.06
2X40	99.06	101.60

ANGLES	±3°	SIZE	A4
LINEAR	0.0 ±0.38	SCALE	4:1
	0.00±0.25	SHEET	1/1

DCC. NO.
A4 DRAWING NO.

MATERIAL		GOLDSUN ELECTRONICS CO., LTD.	
JAMECO NO. 70827		GOLDSUN NO. 22P850003-A	
DRAWN: Kiki Chen		Description FEMALE HEADER	
VERIFY PEOPLE: Ada Zheng , Ivy Lan		Rev. 1	
UNIT: mm	SCALE:	SHEET 1 OF 1	CAS No: ERN No: