





JKL PART NUMBER	- A - LENGTH	COLOR	STARTING CIRCUIT VOLTAGE VS (Vrms)	OPERATING LAMP VOLTAGE VL (Vrms)	OPERATING LAMP CURRENT IL (mAmps)	BRIGHTNESS (CANDELA/m2)	*RATED LIFE (HRS) TYPICAL
BF2261-24B	61±1.5	RGB HIGH OUTPUT WHITE 8400° KELVIN	600 @ 0°C	200	5 ± 1	38,000±10%	50,000
BF22140-24B	140±3.0		990 @ 0°C	330	5 ± 1	38,000±10%	50,000
BF22160-24B	160±3.0		1065 @ 0°C	355	5 ± 1	38,000±10%	50,000
BF22258-24B	258 ^{+3.0} _{-0.0}		1600 @ 0°C	535	5 ± 1	38,000±10%	50,000

*NOTE: RATED LIFE IS DEFINED AS THE POINT AT WHICH THE INTENSITY BECOMES 50% OF THE INITIAL RATING.

			METRIC  THIRD ANGLE PROJECTION		DIMENSIONS ARE IN MILLIMETERS TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- 0.2 2 PL +/- 0 ANGLE +/- 0		JKL COMPONENTS CORPORATION TITLE MINIATURE COLD CATHODE FLUORESCENT LAMP												
D	RATED LIFE HRS. TO TYPICAL & 20,000 TO 50,000		8/19/09		DRAWN BY L. WENGSTROM	APPV'D BY DATE L.R. 8/19/09	SIZE A	FSCM NO. 55335	DRAWING NO. BF 22-24B										
C	ADD MINIMUM TO RATED LIFE HRS.		7/16/09																
B	ADD BF2261-24B		6/19/04																
A	CORRECTION ON LENGTH DIM.		10/7/03																
RELEASED TO CAD MULTI LIST			8/18/03		- CAD DRAWING - MANUAL REVISIONS NOT PERMITTED														
REV. NO.	DESCRIPTION/ECO NUMBER		APPV'D DATE																
SCALE										NONE		RELEASED DATE 8/18/03		REVISION DATE 8/19/09		REV. NO. D		SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JKL Components:](#)

[BF2661-24B](#)