

MODEL NO.	ATTENUATION	BANDWIDTH MHz	INPUT CAPACITANCE	VOLTAGE MAX. DC + AC PK	READ OUT	CABLE LENGTH METERS
6551	X10	500	10 Pf	500	YES	1.2
6554	X10	500	10 Pf	500	NO	1.2
6552	ACCESSORY KIT					

FEATURES:

- Small probe size is ideal for testing in hard to access areas.
- A set of accessories is included with each probe.
- As a minimum all probes meet IEC1010-2-031, 500 V CAT I, 300V CAT II.


RATINGS:

Maximum voltage must be derated with respect to frequency.


ORDERING INFORMATION: Model 6551, 6552, 6554

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02$ " (.51 mm), .xxx = $\pm .005$ " (.127 mm).
All specifications are to the latest revisions. Specifications are subject to change without notice.
Registered trademarks are the property of their respective companies. Made in USA


OSCILLOSCOPE PROBE ACCESSORIES




RETRACTABLE HOOK TIP




BNC ADAPTER




I.C. ADAPTER




INSULATING TIP




TRIMMER TOOL



6" GROUND LEAD



SPRING



PROBE TIPS

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02$ " (.51 mm), .xxx = $\pm .005$ " (.127 mm).
All specifications are to the latest revisions. Specifications are subject to change without notice.
Registered trademarks are the property of their respective companies. Made in USA