

main menu



home
 test & measurement
 products
 skills
 download

online catalogue T&M

clamp-type test probes

crocodile clips

- ▶ 0,64 mm system
- ▶ 2 mm system
- ▶ 4 mm system
- ▶ 4 mm safety system

test probes

oscilloscope test probes

measuring leads

plugs

sockets

sets

miscellaneous

company

portrait

corporate association

location maps

fairs and exhibitions

jobs

imprint

terms and conditions

Home ▶ crocodile clips ▶ crocodile clips ▶ AGF 2


AGF 2

datasheet for AGF 2
 article number: 931272101



[View Full-Size Image](#)



product description:	Bestellnummer: 931 272-101
description:	Extra-fine alligator clip, particularly suited for gripping densely packed extremely small contact points. Contact tongues insulated on the outside to prevent short circuits. Plug connection through 2 mm and 4 mm diameter connectors.
typ:	AGF 2 rot/red
system:	2 mm and 4 mm system
order number:	931 272-101
clamping range:	4 mm
color versions:	
technical data	
type of contact:	clamp
type of termination:	2 mm and 4 mm socket (unsprung)
rated voltage:	30 VAC / 60 VDC
rated current:	6 A
contact resistance:	300 mOhm
material	
contact material:	stainless steel
housing material:	PVC - P
environmental conditions:	
temperature range:	-25 °C to +80 °C
drawing	

search online catalogue

Search

Messetermine

SPS/IPC/DRIVES
 24. 11. 2016 - 24.
 11. 2016

QR-Code

