

3 4 5 2 P + E 3 P + E 3 P + N + E			Ampère	Poles	110 V 50 a. 60 Hz 3pole 4pole 5pole 4h 4h 4h	230 V 50 a. 60 Hz 3pole 4pole 5pole 6h 9h 9h	400 V 50 a. 60 Hz 3pole 4pole 5pole 9h 6h 6h	500 V 50 a. 60 Hz 3pole 4pole 5pole 7h 7h 7h	> 50 - 500 V 100 - 300 Hz 3pole 4pole 5pole 10h 10h 10h	> 50 - 500 V over 300 - 500 Hz 3pole 4pole 5pole 2h 2h 2h		
Part numbers												
	16	3		400 306						1	233	
	16	4			400 406					1	249	
	16	5			400					1	259	
Explanation of the part number suffixes: without suffix = RAL 7035 light grey Use the suffixes to order other colourings: RW = RAL 9010 clear white, CW = RAL 9001 cream white, LA = lacquered aluminium mondo channel installation sockets IP 44  for TEHALIT steel sheet channel, with label												
	16	3		402 306						1	255	
	16	4			402 406					1	271	
	16	5			402					1	281	
Explanation of the part number suffixes: without suffix = RAL 7035 light grey Use the suffixes to order other colourings: RW = RAL 9010 clear white, CW = RAL 9001 cream white, LA = lacquered aluminium mondo channel installation sockets IP 44  for TEHALIT steel sheet channel, with label & lock												
	16	3		401 306						1	233	
	16	4			401 406					1	249	
	16	5			401					1	259	
Explanation of the part number suffixes: without suffix = RAL 7035 light grey Use the suffixes to order other colourings: RW = RAL 9010 clear white, CW = RAL 9001 cream white, LA = lacquered aluminium mondo channel installation sockets IP 44  for TEHALIT plastic channels, with label												
	16	3		403 306						1	255	
	16	4			403 406					1	271	
	16	5			403					1	281	
Explanation of the part number suffixes: without suffix = RAL 7035 light grey Use the suffixes to order other colourings: RW = RAL 9010 clear white, CW = RAL 9001 cream white, LA = lacquered aluminium mondo channel installation sockets IP 44  for TEHALIT plastic channels, with label & lock												



Type 400LA installed in cable channel



Ampère	Poles	110 V 50 a. 60 Hz 3pole 4h 4h 4h	230 V 50 a. 60 Hz 3pole 4h 4h 4h	400 V 50 a. 60 Hz 3pole 4h 4h 4h	500 V 50 a. 60 Hz 3pole 4h 4h 4h	> 50 - 500 V 100 - 300 Hz 3pole 4h 4h 4h	> 50 - 500 V over 300 - 500 Hz 3pole 4h 4h 4h		
--------	-------	--	--	--	--	--	---	--	--

4



430

Part numbers									
16	3	411 304	411 306	411 309				10	128
16	4	410 404	410 409	410 406	410 407	410 410	410 402	10	160
16	5	410 504	410 509	410				10	165
16	5	410 NI (with nickel plated contacts + glass-fibre reinforced enclosure)							10 165
32	3	430 304	430 306	430 309				10	208
32	4	430 404	430 409	430 406	430 407	430 410	430 402	10	215
32	5	430 504	430 509	430				10	226
32	5	430 NI (with nickel plated contacts + glass-fibre reinforced enclosure)							10 226

Panel sockets straight ▲ IP 44, fingerproof acc. to BGV A3



460

63	3	460 304	460 306	460 309				5	586
63	4	460 404	460 409	460 406	460 407	460 410	460 402	5	645
63	5	460 504	460 509	460				5	776
63	5	460 NI (with nickel plated contacts + glass-fibre reinforced enclosure)							5 776

Panel sockets straight ▲ IP 44, fingerproof acc. to BGV A3



431

16	4	411 404	411 409	411 406	411 407	411 410	411 402	10	200
16	5	411 504	411 509	411				10	218
32	3	431 304	431 306	431 309				10	223
32	4	431 404	431 409	431 406	431 407	431 410	431 402	10	230
32	5	431 504	431 509	431				10	283

Panel sockets straight ▲ IP 44, fingerproof acc. to BGV A3, flange screwed on



410 306

16	3	410 304	410 306	410 309				10/60	117
16	3	412 304	412 306	412 309 (flange screwed on)				10	129

Panel sockets straight IP 44 ▲, fingerproof acc. to BGV A3



435

16	3	415 304	415 306	415 309				10	200
16	4	415 404	415 409	415 406	415 407	415 410	415 402	10	214
16	5	415 504	415 509	415				10	263
32	3	435 304	435 306	435 309				10	265
32	4	435 404	435 409	435 406	435 407	435 410	435 402	10	271
32	5	435 504	435 509	435				10	276

mondo panel sockets straight IP 44 ▲, RAL 7035 light grey



417306

16	3	417 304	417 306	417 309				10	153
----	---	---------	----------------	---------	--	--	--	----	-----

mondo panel sockets IP 44 ▲, also for installation channel, RAL 7035 light grey



10003

16	2		10 003	blue				10	46
16	2		10 001	grey				10	46
			10 014	protection against accidental contact for Schuko sockets				1	3
16	2		10 005	blue, with extra flange	fixing dimensions = 60 x 60 mm,			10	70
16	2		10 006	grey, with extra flange	flange dimensions = 75 x 75 mm			10	70

Earthing contact sockets IP 44 ▲, panel socket straight



10004

16	2		10 004					10	94
----	---	--	---------------	--	--	--	--	----	----

Earthing contact socket IP 44 ▲, mondo panel sockets straight, RAL 7035 light grey



Ampère	Poles	110 V 50 a. 60 Hz	230 V 50 a. 60 Hz	400 V 50 a. 60 Hz	500 V 50 a. 60 Hz	> 50 - 500 V 100 - 300 Hz	> 50 - 500 V over 300 - 500 Hz		
		3pole 4h 4pole 4h 5pole 4h	3pole 6h 4pole 9h 5pole 9h	3pole 9h 4pole 6h 5pole 6h	3pole 7h 4pole 7h 5pole 7h	3pole 10h 4pole 10h 5pole 10h	3pole 2h 4pole 2h 5pole 2h		

Part numbers											
	16	3	510 304	510 306	510 309				10	120	
	16	4	510 404	510 409	510 406	510 407	510 410	510 402	10	160	
	16	5	510 504	510 509	510				10	175	
	16	5	510 NI (with nickel plated contacts + glass-fibre reinforced enclosure)						10	175	
	32	3	530 304	530 306	530 309				10	207	
	32	4	530 404	530 409	530 406	530 407	530 410	530 402	10	216	
	32	5	530 504	530 509	530				10	240	
	32	5	530 NI (with nickel plated contacts + glass-fibre reinforced enclosure)						10	240	
	Panel sockets angled IP 44 ▲, fingerproof acc. to BGV A3										
		16	4	511 404	511 409	511 406	511 407	511 410	511 402	10	181
16		5	511 504	511 509	511				10	201	
32		3	531 304	531 306	531 309				10	218	
32		4	531 404	531 409	531 406	531 407	531 410	531 402	10	236	
32		5	531 504	531 509	531				10	254	
63		3	560 304	560 306	560 309				5	593	
63		4	560 404	560 409	560 406	560 407	560 410	560 402	5	677	
63		5	560 504	560 509	560				5	708	
63		5	560 NI (with nickel plated contacts + glass-fibre reinforced enclosure)						5	708	
Panel sockets angled IP 44 ▲, fingerproof acc. to BGV A3											
 	16	5	512 504	512 509	512				10	198	
	16	5	512 NI (with nickel plated contacts + glass-fibre reinforced enclosure)						10	198	
	32	5	532 504	532 509	532				10	259	
	32	5	532 NI (with nickel plated contacts + glass-fibre reinforced enclosure)						10	259	
	63	5	562 504	562 509	562				5	715	
	63	5	562 NI (with nickel plated contacts + glass-fibre reinforced enclosure)						5	715	
	► Suitable mounting block for panel sockets with fixing dimensions 90 x 90 mm: part no. 562 500										
	Panel sockets angled IP 44 ▲, 16 - 63 A fingerproof acc. to BGV A3										
		16	3	514 304	514 306	514 309				10	158
		16	4	514 404	514 409	514 406	514 407	514 410	514 402	10	202
16		5	514 504	514 509	514				10	220	
32		3	534 304	534 306	534 309				10	300	
32		4	534 404	534 409	534 406	534 407	534 410	534 402	10	285	
32		5	534 504	534 509	534				10	305	
Panel sockets angled IP 44 ▲, flange screwed on											
		63	3	564 304	564 306	564 309				5	646
		63	4	564 404	564 409	564 406				5	695
		63	5	564 504	564 509	564				5	744
	Panel sockets angled IP 44 ▲, flange screwed on										
		16	3	512 304	512 306	512 309				10	120
		Panel sockets angled IP 44 ▲, with evehook for padlock									
		16	3	512 304	512 306	512 309				10	120



Ampère	Poles	110 V 50 a. 60 Hz	230 V 50 a. 60 Hz	400 V 50 a. 60 Hz	500 V 50 a. 60 Hz	> 50 - 500 V 100 - 300 Hz	> 50 - 500 V over 300 - 500 Hz		
		3pole 4h 4pole 4h 5pole 4h	3pole 6h 4pole 9h 5pole 9h	3pole 9h 4pole 6h 5pole 6h	3pole 7h 4pole 7h 5pole 7h	3pole 10h 4pole 10h 5pole 10h	3pole 2h 4pole 2h 5pole 2h		

Part numbers



16	3	419 304	419 306	419 309				10	139
16	4	419 404	419 409	419 406	419 407	419 410	419 402	10	186
16	5	419 504	419 509	419				10	202
16	5	419 NI (with nickel plated contacts + glass-fibre reinforced enclosure)						10	202
32	3	439 304	439 306	439 309				10	246
32	4	439 404	439 409	439 406	439 407	439 410	439 402	10	252
32	5	439 504	439 509	439				10	278
32	5	439 NI (with nickel plated contacts + glass-fibre reinforced enclosure)						10	278
63	3	469 304	469 306	469 309				5	599
63	4	469 404	469 409	469 406	469 407	469 410	469 402	5	699
63	5	469 504	469 509	469				5	799
63	5	469 NI (with nickel plated contacts + glass-fibre reinforced enclosure)						5	799

Panel sockets straight IP 67 (fingerproof acc. to BGV A3)



125	3	479 304	479 306	479 309				2	990
125	4	479 404	479 409	479 406	479 407	479 410	479 402	2	1155
125	5	479 504	479 509	479				2	1319
125	5	479 NI (with nickel plated contacts + glass-fibre reinforced enclosure)						2	1319

Panel sockets straight IP 67 (with multi contact, fingerproof acc. to BGV A3)



16	3	519 304	519 306	519 309				10	142
16	4	519 404	519 409	519 406	519 407	519 410	519 402	10	257
16	5	519 504	519 509	519				10	223
16	5	519 NI (with nickel plated contacts + glass-fibre reinforced enclosure)						10	223
32	3	539 304	539 306	539 309				10	263
32	4	539 404	539 409	539 406	539 407	539 410	539 402	10	287
32	5	539 504	539 509	539				10	303
32	5	539 NI (with nickel plated contacts + glass-fibre reinforced enclosure)						10	303
63	3	569 304	569 306	569 309				5	638
63	4	569 404	569 409	569 406	569 407	569 410	569 402	5	725
63	5	569 504	569 509	569				5	832
63	5	569 NI (with nickel plated contacts + glass-fibre reinforced enclosure)						5	832

Panel sockets angled IP 67 (fingerproof acc. to BGV A3)




125	3	579 304	579 306	579 309				2	988
125	4	579 404	579 409	579 406	579 407	579 410	579 402	2	1152
125	5	579 504	579 509	579				2	1316
125	5	579 NI (with nickel plated contacts + glass-fibre reinforced enclosure)						2	1316

Panel sockets angled IP 67 (with multi contact, fingerproof acc. to BGV A3)



16	4	517 404	517 409	517 406	517 407	517 410	517 402	10	194
16	5	517 504	517 509	517				10	212
32	3	537 304	537 306	537 309				10	255
32	4	537 404	537 409	537 406	537 407	537 410	537 402	10	273
32	5	537 504	537 509	537				10	293
63	5	567 504	567 509	567				5	843

Panel sockets angled IP 67 (fingerproof acc. to BGV A3)



16	3	518 304	518 306	518 309				10	238
16	4	518 404	518 409	518 406	518 407	518 410	518 402	10	256
16	5	518 504	518 509	518				10	274
32	3	538 304	538 306	538 309				10	339
32	4	538 404	538 409	538 406	538 407	538 410	538 402	10	330
32	5	538 504	538 509	538				10	350
63	3	568 304	568 306	568 309				5	661
63	4	568 404	568 409	568 406	568 407	568 410	568 402	5	720
63	5	568 504	568 509	568				5	779

Panel sockets angled IP 67 (flange screwed on)