



AUO Solar

e-News

Language

English

Search

Go

[About AUO](#)[Citizenship](#)[Product](#)[Technology](#)[Investor](#)[Career](#)[Support](#)[Home](#) > [Product Applications](#) > [TFT-LCD](#) > [General Display](#) > [General Display](#) > [G121XN01 V0](#)[About AUO](#)[Citizenship](#)[Product Applications](#)[Product Introduction](#)[TFT-LCD](#)[LCD TV](#)[PID](#)[Monitor](#)[Notebook PC](#)[General Display](#)[Mobile Device](#)[DSC](#)[Printer](#)[Car](#)[PND](#)[DPF](#)[E-Paper](#)[Solar](#)[Technology](#)[Investor Relations](#)[Career](#)[Support](#)

G121XN01 V0

[General Display](#)

Model	G121XN01 V0
Size	12.1"
Resolution (pixel)	XGA (1024 x 768)
Active Area	245.8 x 184.3
Pixel Pitch (mm)	0.24
Mode	TN
Number of Colors	262K / 16.2M
Color Saturation (%)	70
Viewing Angle (H/V)	160 / 160
Brightness (cd/m²)	500
Contrast Ratio	700 : 1
Response Time (ms)	35
Power Consumption (W)	9.2
Interface	LVDS
Supply Voltage (v)	3.3
Light Source	LED
Outline Dimension (mm)	279 x 209 x 9
Weight (g)	495
Production	Now
Remark	Reverse Scan Replaceable Lamp 6/8 bit Convertible Wide Temperature RGBW

Related Links

[Technology](#)[Awards](#)

Reference

[Contact AUO](#)