



**NOTES:**

**MATERIAL**  
 1. Insulator Material: PBT+30%G.F.(UL94V-0), Grey  
 2. Contact Material : Brass  
 3. Contact Plating : Gold Flash / Tin Over Ni

**ELECTRICAL**  
 1. Current Rating : 3.0AMP  
 2. Withstand Voltage : 1000V AC/minute  
 3. Contact Resistance : 20mΩ max  
 4. Insulation Resistance: 1000MΩ min

**ENVIRONMENTAL**  
 1. Operation Temperature: -40°C to +105°C  
 2. Packing : Tray  
 3. No side slot "A" and "B" from 6 to 16 pin  
 No side slot "A" from 18 to 58 pin

**Ordering Information**

AWH xxA-02x2-T

No. of Contacts	Latch Type
06 08	0(w/o latch)
10 12	2(with short latch)
14 16	2(with short latch)
18 20	3(with long latch)
24 26	
30 34	
40 50	
60 64	

**RoHS compliant**

Scale	1:1	⑥	Add special PCB layout	07.12.2010	Alex		Date	Name	Customer-No.
TOLERANCE		⑤	Correct drawing of short latch	05.05.2010	Dean	Drawn	25.01.2006	Alex	
X.X	±0.40	④	Change dimension	27.10.2009	Dean	Approved	07.12.2010	Gerber	ASSMANN WSW-No. <b>AWH xxA-02x2-T</b>
X.XX	±0.25	③	Correct No. of contacts	29.06.2009	Dean				
X.XXX	±0.15	③	Correct No. of contacts	29.06.2009	Dean				Drawing-No.
Angle	±3°	②	Update	21.05.2009	Rate				
		①	Drawn	25.01.2006	Alex				ASS 2311 CO rev06
		Id.	Modification	Date	Name				

