




DESIGNED FOR USE WITH .141 DIA S/R CABLE	
CABLE ENTRY DIAMETER MINIMUM	
HOUSING	.143
CONTACT	.037

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
01 ₀	RELEASED	10/4/95	<i>DCornell</i>

.XXX = in
XX.X = mm

HOUSING	STAINLESS STEEL PER ASTM-A484 AND ASTM- A582, TYPE 303	GOLD PLATE PER MIL-G-45204
DIELECTRIC	TFE FLUOROCARBON PER ASTM-D-1457	N/A
CENTER CONTACT	BERYLLIUM COPPER PER ASTM B 196, ALLOY C17300, CONDITION H	GOLD PLATE PER MIL-G-45204
COMPONENT	MATERIAL	FINISH
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCE ON FRAC. DEC. ANGLES ± 1/64 ±.005 ± 1°	DRAWN BY <i>ADP</i> DATE 10/3/95	 AMP Incorporated 140 Fourth Avenue Waltham, MA 02451-7599
	CHECKED BY	
	APPD BY <i>DCornell</i> 10/4/95	
These drawings and specifications are the property of M/A-COM Incorporated and shall not be reproduced or copied or used in whole or in part as the basis for the manufacture or sale of item(s) without written permission.	USE ASS'Y PROCEDURE	TITLE OSM 27 GHz STRAIGHT CABLE JACK - DIRECT SOLDER ATTACHMENT
	408-04872 NO. AP. (27-003)	SIZE B CODE IDENT NO. 26805 2702-7941-00 REV 01 ₀
		SCALE 4:1 SHEET 1 OF 1

NOTES:
1. NON-CAPTURD CENTER CONTACT