



See The Video


www.L-com.com/Videos/A14



Item #	Description	1-9	10-24	25-99	100-249	250-499
--------	-------------	-----	-------	-------	---------	---------

Premium D-Sub Cable Assemblies - Fully Populated and Double Shielded

The CS2N Series of D-Sub cable assemblies is our top of the line D-Sub cabling offering. These cables offer the best features for those applications where only the best will do. The bulk cable utilizes 26AWG stranded conductors with double shielding (copper braid plus aluminum mylar foil) and flexible PVC jacket. Fully molded backshells also have a unique stamped steel internal enclosure that provides the ultimate in shielding performance. Mounting is done via rugged 4-40 thumbscrews that are easy to grip without the need for a screwdriver. Hex nuts on female connectors are removable to expose 4-40 thumbscrews. Color: Light Gray.



RoHS Premium 9 Pin D-Sub Cables - Molded, Fully Populated and Double Shielded

CS2N9MM-2.5	Premium Molded Cable, DB9 Male / Male, 2.5 ft	16.25	15.27	14.30	13.33	12.35
CS2N9MM-5	Premium Molded Cable, DB9 Male / Male, 5.0 ft	18.50	17.39	16.28	15.17	14.06
CS2N9MM-6	Premium Molded Cable, DB9 Male / Male, 6.0 ft	19.40	18.24	17.07	15.91	14.74
CS2N9MM-10	Premium Molded Cable, DB9 Male / Male, 10.0 ft	23.00	21.62	20.24	18.86	17.48
CS2N9MM-12	Premium Molded Cable, DB9 Male / Male, 12.0 ft	24.80	23.31	21.82	20.34	18.85
CS2N9MM-15	Premium Molded Cable, DB9 Male / Male, 15.0 ft	27.50	25.85	24.20	22.55	20.90
CS2N9MM-25	Premium Molded Cable, DB9 Male / Male, 25.0 ft	36.50	34.31	32.12	29.93	27.74
CS2N9MM-50	Premium Molded Cable, DB9 Male / Male, 50.0 ft	59.00	55.46	51.92	48.38	44.84
CS2N9MF-2.5	Premium Molded Cable, DB9 Male / Female, 2.5 ft	16.25	15.27	14.30	13.33	12.35
CS2N9MF-5	Premium Molded Cable, DB9 Male / Female, 5.0 ft	18.50	17.39	16.28	15.17	14.06
CS2N9MF-6	Premium Molded Cable, DB9 Male / Female, 6.0 ft	19.40	18.24	17.07	15.91	14.74
CS2N9MF-10	Premium Molded Cable, DB9 Male / Female, 10.0 ft	23.00	21.62	20.24	18.86	17.48
CS2N9MF-12	Premium Molded Cable, DB9 Male / Female, 12.0 ft	24.80	23.31	21.82	20.34	18.85
CS2N9MF-15	Premium Molded Cable, DB9 Male / Female, 15.0 ft	27.50	25.85	24.20	22.55	20.90
CS2N9MF-25	Premium Molded Cable, DB9 Male / Female, 25.0 ft	36.50	34.31	32.12	29.93	27.74
CS2N9MF-50	Premium Molded Cable, DB9 Male / Female, 50.0 ft	59.00	55.46	51.92	48.38	44.84

RoHS Premium High Density 15 Pin D-Sub Cables - Molded, Fully Populated and Double Shielded

CS2H15MM-2.5	Premium Molded Cable, HD15 Male / Male, 2.5 ft	20.50	19.27	18.04	16.81	15.58
CS2H15MM-5	Premium Molded Cable, HD15 Male / Male, 5.0 ft	23.00	21.62	20.24	18.86	17.48
CS2H15MM-6	Premium Molded Cable, HD15 Male / Male, 6.0 ft	24.00	22.56	21.12	19.68	18.24
CS2H15MM-10	Premium Molded Cable, HD15 Male / Male, 10.0 ft	28.00	26.32	24.64	22.96	21.28
CS2H15MM-12	Premium Molded Cable, HD15 Male / Male, 12.0 ft	30.00	28.20	26.40	24.60	22.80
CS2H15MM-15	Premium Molded Cable, HD15 Male / Male, 15.0 ft	33.00	31.02	29.04	27.06	25.08
CS2H15MM-25	Premium Molded Cable, HD15 Male / Male, 25.0 ft	43.00	40.42	37.84	35.26	32.68
CS2H15MM-50	Premium Molded Cable, HD15 Male / Male, 50.0 ft	68.00	63.92	59.84	55.76	51.68
CS2H15MF-2.5	Premium Molded Cable, HD15 Male / Female, 2.5 ft	20.50	19.27	18.04	16.81	15.58
CS2H15MF-5	Premium Molded Cable, HD15 Male / Female, 5.0 ft	23.00	21.62	20.24	18.86	17.48
CS2H15MF-6	Premium Molded Cable, HD15 Male / Female, 6.0 ft	24.00	22.56	21.12	19.68	18.24
CS2H15MF-10	Premium Molded Cable, HD15 Male / Female, 10.0 ft	28.00	26.32	24.64	22.96	21.28
CS2H15MF-12	Premium Molded Cable, HD15 Male / Female, 12.0 ft	30.00	28.20	26.40	24.60	22.80
CS2H15MF-15	Premium Molded Cable, HD15 Male / Female, 15.0 ft	33.00	31.02	29.04	27.06	25.08
CS2H15MF-25	Premium Molded Cable, HD15 Male / Female, 25.0 ft	43.00	40.42	37.84	35.26	32.68
CS2H15MF-50	Premium Molded Cable, HD15 Male / Female, 50.0 ft	68.00	63.92	59.84	55.76	51.68

Note: Cables utilizing coaxial signal lines are recommended for video monitors.

RoHS Premium 25 Pin D-Sub Serial Parallel Cables - Molded, Fully Populated and Double Shielded

CS2N25MM-2.5	Premium Molded Cable, DB25 Male / Male, 2.5 ft	22.50	21.15	19.80	18.45	17.10
CS2N25MM-5	Premium Molded Cable, DB25 Male / Male, 5.0 ft	25.00	23.50	22.00	20.50	19.00
CS2N25MM-6	Premium Molded Cable, DB25 Male / Male, 6.0 ft	26.00	24.44	22.88	21.32	19.76
CS2N25MM-10	Premium Molded Cable, DB25 Male / Male, 10.0 ft	30.00	28.20	26.40	24.60	22.80
CS2N25MM-12	Premium Molded Cable, DB25 Male / Male, 12.0 ft	32.00	30.08	28.16	26.24	24.32
CS2N25MM-15	Premium Molded Cable, DB25 Male / Male, 15.0 ft	35.00	32.90	30.80	28.70	26.60
CS2N25MM-25	Premium Molded Cable, DB25 Male / Male, 25.0 ft	45.00	42.30	39.60	36.90	34.20
CS2N25MM-50	Premium Molded Cable, DB25 Male / Male, 50.0 ft	70.00	65.80	61.60	57.40	53.20
CS2N25MF-2.5	Premium Molded Cable, DB25 Male / Female, 2.5 ft	22.50	21.15	19.80	18.45	17.10
CS2N25MF-5	Premium Molded Cable, DB25 Male / Female, 5.0 ft	25.00	23.50	22.00	20.50	19.00
CS2N25MF-6	Premium Molded Cable, DB25 Male / Female, 6.0 ft	26.00	24.44	22.88	21.32	19.76
CS2N25MF-10	Premium Molded Cable, DB25 Male / Female, 10.0 ft	30.00	28.20	26.40	24.60	22.80
CS2N25MF-12	Premium Molded Cable, DB25 Male / Female, 12.0 ft	32.00	30.08	28.16	26.24	24.32
CS2N25MF-15	Premium Molded Cable, DB25 Male / Female, 15.0 ft	35.00	32.90	30.80	28.70	26.60
CS2N25MF-25	Premium Molded Cable, DB25 Male / Female, 25.0 ft	45.00	42.30	39.60	36.90	34.20
CS2N25MF-50	Premium Molded Cable, DB25 Male / Female, 50.0 ft	70.00	65.80	61.60	57.40	53.20

RoHS Premium 37 Pin D-Sub Serial Parallel Cables - Molded, Fully Populated and Double Shielded

CS2N37MM-2.5	Premium Molded Cable, DB37 Male / Male, 2.5 ft	38.75	36.42	34.10	31.78	29.45
CS2N37MM-5	Premium Molded Cable, DB37 Male / Male, 5.0 ft	42.50	39.95	37.40	34.85	32.30
CS2N37MM-10	Premium Molded Cable, DB37 Male / Male, 10.0 ft	50.00	47.00	44.00	41.00	38.00
CS2N37MM-15	Premium Molded Cable, DB37 Male / Male, 15.0 ft	57.50	54.05	50.60	47.15	43.70
CS2N37MM-25	Premium Molded Cable, DB37 Male / Male, 25.0 ft	72.50	68.15	63.80	59.45	55.10
CS2N37MM-50	Premium Molded Cable, DB37 Male / Male, 50.0 ft	110.00	103.40	96.80	90.20	83.60
CS2N37MF-2.5	Premium Molded Cable, DB37 Male / Female, 2.5 ft	38.75	36.42	34.10	31.78	29.45
CS2N37MF-5	Premium Molded Cable, DB37 Male / Female, 5.0 ft	42.50	39.95	37.40	34.85	32.30
CS2N37MF-10	Premium Molded Cable, DB37 Male / Female, 10.0 ft	50.00	47.00	44.00	41.00	38.00
CS2N37MF-15	Premium Molded Cable, DB37 Male / Female, 15.0 ft	57.50	54.05	50.60	47.15	43.70
CS2N37MF-25	Premium Molded Cable, DB37 Male / Female, 25.0 ft	72.50	68.15	63.80	59.45	55.10
CS2N37MF-50	Premium Molded Cable, DB37 Male / Female, 50.0 ft	110.00	103.40	96.80	90.20	83.60

Shop at **L-com.com** or call **1-800-343-1455**

E-mail: sales@L-com.com Fax: 978-689-9484

"I love all the extra information you put in your catalogs and how you also make it available for download as PDF files. I feel like I get an education just reading your catalog!" - Farren C.