





FRONT VIEW




TABLE

ITEM NO	L
3073-2S	2000mm±30mm
3073-3	3000mm±30mm
3073-5	5000mm±30mm
3073-10	10000mm±30mm
3073-15	15000mm±30mm
3073-20	20000mm±30mm



FRONT VIEW



HEAT SEALED

PIN OUT

MINI6PIN PLUG(P1)	WIRE	MINI6PIN JACK(J1)
1		1
2		2
3		3
4		4
5		5
6		6
SHELL	DRAIN WIRE	SHELL

1.CABLE:ND UL,28AWG/7/0.127,TINNED AND STRANDED COPPER WIRE
INSULATOR:PVC,1D:0.85mm ,CABLING:6C+DRAIN WIRE
SHEILD:MY COVERAGE
JACKET:PVC, COMPLIANCE ROHS,COLOR:BEIGE,D.D:5mm
2.1PCS CONNECTOR:MINI 6 PIN MALE SOLDER TYPE CONNECTOR
INSULATOR:P.B.T+GLASS FIBER,COLOR:BLACK
CONTACT:COOPER ALLOY NICKEL PLATED
SHELL:BRASS,NICKEL PLATED
CONNECTOR COMPLIANCE ROHS
3.1PCS CONNECTOR:MINI 6 PIN FEMALE SOLDER TYPE CONNECTOR
INSULATOR:P.B.T+GLASS FIBER,COLOR:BLACK
CONTACT:COOPER ALLOY NICKEL PLATED
SHELL:BRASS,NICKEL PLATED
CONNECTOR COMPLIANCE ROHS
4.HOOD:PVC,MOLDDED TYPE, COMPLIANCE ROHS,COLOR:BEIGE
5.FULL ROHS Guideline
6.ELECTRONIC TEST
100% OPEN SHORT+MISS WIRE TEST

PART NO

SHEET NO 1

THIRD ANGLE PROJECTION

TITLE: P/S2 6 PIN MALE TO P/S2 6 PIN FEMALE

BEIGE COLOR

DWN NO

SCALE: N.T.S.
SIZE: A4
UNIT: mm INCH

CHECKED BY & DATE
APPROVED BY & DATE