






6766



5366NCR



14W33



1533

Industrial Specification Grade Straight Blade Plugs & Connectors

2-Pole, 3-Wire Grounding
20A, 125V/AC
NEMA 5-20



5-20P



5-20R

Industrial Grade Plugs & Connectors

Safety Grip™ NEMA 5-20



Rating A	V/AC	Product Type & Cord Diameter	Color	Plug	Catalog No.	Connector
20	125	Straight Body 0.33-0.66" (6.4-16.7mm)	Black & White	□ 6766	•	□ 6769 •

AutoGrip™ NEMA 5-20



Rating A	V/AC	Product Type & Cord Diameter	Color	Plug	Catalog No.	Connector
20	125	Straight Body 0.33-0.66" (6.4-16.7mm)	Black & White	□ 5366N	•	□ 5369N •
		Corrosion Resistant, Straight Body 0.33-0.66" (6.4-16.7mm)	Yellow	□ 5366NCR	•	□ 5369NCR •

Watertight NEMA 5-20



Rating A	V/AC	Product Type & Cord Diameter	Color	Plug	Catalog No.	Connector
20	125	Straight Body 0.30-0.65" (7.6-16.5mm)	Yellow	□ 14W33	•	□ 15W33 •
		Straight Body 0.30-0.65" (7.6-16.5mm)	Black	□ 14W33BK	•	□ 15W33BK •

Severe Duty NEMA 5-20



Rating A	V/AC	Product Type & Cord Diameter	Color	Plug	Catalog No.	Connector
20	125	Straight Body 0.38-1.00" (19.1-25.4mm)	Yellow & Black	□ 1433	•	□ 1533 •

Icon Key

NAFTA Compliant - see page O-30

Accessories for Industrial Grade NEMA 5-15 Plugs & Connectors

Description	Catalog No.
Watertight plug closure cap for 20A plug	□ 14W •
Replacement watertight connector closure cap for 20A connector	□ 15W •
Wire mesh grip for 20A watertight plugs & connectors, 0.30-0.50" (7.6-12.7mm) cord dia.	□ WM115 •
Wire mesh grip for 20A watertight plugs & connectors, 0.50-0.62" (12.7-15.8mm) cord dia.	□ WM116 •



14W



15W



WM115



WM116

Industrial Grade Dimensional
Information: B-18

Specification Information:

Safety Grip Industrial Plugs &
Connectors: B-26

AutoGrip Industrial Plugs &
Connectors: B-26

Corrosion Resistant AutoGrip
Industrial Plugs &
Connectors: B-29

Watertight Industrial Plugs &
Connectors: B-28

Severe Duty Industrial
Plugs & Connectors: B-29