





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
FT	0		CI	REVISED PER ECO-12-007964	02MAY2012	KH	MS



- 1
- MATERIALS AND FINISH
HOUSING: PA 6-6, UL 94-V0, COLOR GREEN.
TERMINAL: COPPER ALLOY, TIN PLATED.
- 2
- SUITABLE FOR 1,6-2,4mm PC BOARD THICKNESS.
- 3
- RECOGNIZED UNDER THE COMPONENT PROGRAM OF
UNDERWRITERS LABORATORIES INC.FILE N° E60677.
- 4
- IMQ CERTIFICATE WITH SURVEILLANCE IN CONFORMITY
WITH IEC 998-1/998-2-1.
- 5
- NOT CUMULATIVE TOLERANCE.




282816-2 AS SHOWN



125	13	1-282816-3
115	12	1-282816-2
105	11	1-282816-1
95	10	1-282816-0
85	9	282816-9
75	8	282816-8
65	7	282816-7
55	6	282816-6
45	5	282816-5
35	4	282816-4
25	3	282816-3
15	2	282816-2
DIM. A		N° OF POS. PART NUMBER

RECOMMENDED PC BOARD LAYOUT



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN E. ZANOLINI 25JUL2001	TE Connectivity			
		CHK D. BIEVENOUR 25JUL2001				
		APVD D. BIEVENOUR 25JUL2001	NAME TERMINAL BLOCK HEADER ASSEMBLY 90 DEGREE CLOSED ENDS 10mm PITCH			
DIMENSIONS: mm		PRODUCT SPEC 108-20166	SIZE A3		CAGE CODE 00779	
		APPLICATION SPEC 114-20079	DRAWING NO C-282816		RESTRICTED TO -	
MATERIAL		WEIGHT -	SCALE 3:1		SHEET 1 OF 1	
		CUSTOMER DRAWING			REV CI	