

Direct Links

Cross Reference

RoHS/LF P/N search

Document & Drawing search

Application tooling

Services

Contact us

Distributor list

Pricing request

Order samples

Literature

Brochures & catalogs

Product documentation

Technical library

Start > [Search=tp1010*](#) > **TP1010Z**

TP1010Z

VIN FL FK 1210, 8-10 ST

ACTIVE

Customer Drawing

RoHS compatible

Electrical division



[Assistant](#)[Add to Favorites](#)

Email Datasheet

Print Datasheet

FCI Brings You More

Contact our sales/technical support...

Sample request

Price request

Download document

Literature

> [Power solutions Product Focus](#)

> [COMPRESSION TERMINAL Brochures](#)

> [Renewable Energy Products Brochure](#)

> [EC&M Catalog](#)

> [Connector Theory and Application Brochure](#)

Application Tooling

> [Electrical Tooling](#)

Specifications

Dimensional	Physical	Approvals / Certifications	Other Features
Dimensional			
Stud Hole (Size)	#10 #8		
Tongue Width (in)	0.41 in.		
Wire Insulation Grip	No		
Insulation Diameter (Max)	0.26 in.		
Physical			
Conductor Size	12 AWG 10 AWG		
Element A Index	Hand Tools		
Insulation Type	PVC		
Color Code	Yellow		
Conductor Size (Range)	12 AWG to 10 AWG		
Approvals / Certifications			
Military Listed	No		
UL Listed	Yes		
CSA Certified	No		
Other Features			
Tape Mounted Catalog Number	BA10EZ10M		
Tongue Type	Flanged Fork		
Bulk Catalog Number	BA10EZ10		
UPC	78181071156		
Keyword	smlterm		