


FEATURES

- P.C. board mounting
- Wave solderable and washable
- Low current consumption




ORDERING INFORMATION

SB	T	16	06	S
SAM BU	TRANSDUCER	MODEL NO.	VOLTAGE	INCIRCUIT TYPE

ELECTRICAL SPECIFICATIONS

All data at 25°C unless otherwise specified.

Parameter	SBT-16S		Unit
	1606S	1612S	
Rated Voltage	6	12	V p-p
Operating Voltage	4~7	8~16	V p-p
Rated Current(MAX)	30		mA
Basic Frequency	2,200±300		Hz
Sound Pressure Level @10cm (MIN)	MIN 85		dBA
Temperature Range			
Operating	-30~+85		°C
Storage	-40~+85		°C



SBT-16(S)

DIMENSIONS

