

HUSD-15BL/BM

DUAL BUTTON HOLD-UP SWITCH





- Dual button activation to eliminate accidental triggering
- SPDT transfer contact for supervised loop
- Terminal strip with three wire terminals
- Tamper protected switch mechanism using UL listed microswitch
- Concealed mounting screw
- Status window indicator
- White plastic case housing
- HUSD-15BL latching button, tool reset (included)
- HUSD-15BM momentary button, auto-reset

The HUSD-15B Series is a Form C (SPDT), dual button hold-up switch that is designed to generate an alarm condition only when both buttons are pressed simultaneously, thus preventing accidental triggering.


The housing of this series is specially designed with a status window, red (alarm) and blue (armed), to verify the switch condition. The housing mounting screw is concealed to provide additional tampering protection. The built-in UL approved microswitch design generates an alarm condition when the cover is removed or damaged. The terminal strip consists of three wire ports that provide a firm and secure wiring installation.

The HUSD-15BL is designed for latching operation when triggered. The HUSD-15BM is designed for momentary operation.

Dimensions



Wire Installation




HUSD-15BL/BM


DUAL BUTTON HOLD-UP SWITCH

Operating Method


Momentary N.O.-Latch Type Micro Switch




Latch Type Micro Switch



Push Red Double Button



Push Red Double Button



Specifications

| Model Number | Stock Number | Mechanism Type | Contact Type | Contact Rating | | | Overall Stroke | Overall Force | Operating Method | Operating Temperature Range |
|--------------|--------------|----------------|-------------------|----------------|--------|---------|----------------|-----------------|------------------|------------------------------|
| | | | | 125V DC | 30V DC | 125V AC | | | | |
| HUSD-15BL | 4370036 | Latching | SPDT N.O./N.C. | 0.4A | 5A | 5A | 3mm | 10.5 - 14 ounce | Dual button | 32°F - 120°F (0°C - 49°C) |
| HUSD-15BM | 4370037 | Momentary | | | | | | | | |