


## Dimensions: mm (In.)

**Electrical Specifications:**

- Rating: .3A/125VAC (\*.3A/30VDC)
- Insulation resistance: 100MΩ/500VDC
- Dielectric strength: 1,000VAC for 1min. (\*500VAC)
- Contact resistance: 20mΩ @ 2.5VDC

**Materials:**

- Contacts & terminals: gold plated

| Mouser Stock No. | Type | Circuit   |
|------------------|------|-----------|
| 10TC405          | SPST | ON-OFF    |
| 10TC410          | SPDT | ON-ON     |
| * 10TC412        | SPDT | ON-OFF-ON |
| 10TC415          | DPDT | ON-ON     |
| * 10TC418        | DPDT | ON-OFF-ON |

**Sub-Miniature Toggle Switches**  
 10TC405, 10TC410, 10TC412, 10TC415, 10TC418

**Mountain  
Switch**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mountain Switch:

[10TC405](#) [10TC415](#) [10TC410](#) [10TC412](#) [10TC418](#)