



HelaGuard Accessories

• CNV Converters

Nickel plated brass.



HelaGuard CNV Convertors.

Technical Table

Article-No.	Type	Thread Size, internal	Thread Size external	Pack Cont.
166-50900	CNV-M20-M16	M16	M20	10
166-50901	CNV-PG7-M16	M16	PG7	10
166-50902	CNV-PG9-M16	M16	PG9	10
166-50903	CNV-PG11-M16	M16	PG11	10
166-50904	CNV-PG13-M16	M16	PG13.5	10
166-50905	CNV-PG16-M16	M16	PG16	10
166-50906	CNV-M16-M20	M20	M16	10
166-50907	CNV-M25-M20	M20	M25	10
166-50908	CNV-PG9-M20	M20	PG9	10
166-50909	CNV-PG11-M20	M20	PG11	10
166-50910	CNV-PG13-M20	M20	PG13.5	10
166-50911	CNV-PG16-M20	M20	PG16	10
166-50912	CNV-PG21-M20	M20	PG21	10
166-50913	CNV-PG29-M20	M20	PG29	2
166-50914	CNV-M20-M25	M25	M20	10
166-50915	CNV-M32-M25	M25	M32	10
166-50916	CNV-M40-M25	M25	M40	10
166-50917	CNV-M50-M25	M25	M50	1
166-50918	CNV-PG16-M25	M25	PG16	10
166-50919	CNV-PG21-M25	M25	PG21	10
166-50920	CNV-PG29-M25	M25	PG29	2
166-50921	CNV-M25-M32	M32	M25	10
166-50922	CNV-M40-M32	M32	M40	2
166-50923	CNV-M50-M32	M32	M50	1
166-50924	CNV-PG21-M32	M32	PG21	2
166-50925	CNV-PG29-M32	M32	PG29	2
166-50926	CNV-PG36-M32	M32	PG36	2
166-50927	CNV-M50-M40	M40	M50	1
166-50928	CNV-M63-M40	M40	M63	1
166-50929	CNV-PG29-M40	M40	PG29	1
166-50930	CNV-PG36-M40	M40	PG36	1
166-50931	CNV-M63-M50	M50	M63	1
166-51012	CNV-M16-PG11	PG11	M16	10
166-51013	CNV-M20-PG11	PG11	M20	10
166-51014	CNV-PG9-PG11	PG11	PG9	10
166-51015	CNV-PG13-PG11	PG11	PG13.5	10
166-51016	CNV-PG16-PG11	PG11	PG16	10
166-51017	CNV-PG21-PG11	PG11	PG21	10
166-51018	CNV-M20-PG13	PG13.5	M20	10
166-51019	CNV-PG11-PG13	PG13.5	PG11	10
166-51020	CNV-PG16-PG13	PG13.5	PG16	10
166-51021	CNV-PG21-PG13	PG13.5	PG21	10

All dimensions in mm. Subject to technical changes.

Material Data

Material	Nickel Plated Brass (NPB)
Colour	Metal (ML)
Operating Temperature	-100 °C to +300 °C





HelaGuard Accessories

• CNV Converters

Nickel plated brass.

Technical Table

Article-No.	Type	Thread Size, internal	Thread Size external	Pack Cont.
166-51022	CNV-M20-PG16	PG16	M20	10
166-51023	CNV-PG13-PG16	PG16	PG13.5	10
166-51024	CNV-PG21-PG16	PG16	PG21	10
166-51025	CNV-PG29-PG16	PG16	PG29	2
166-51026	CNV-M20-PG21	PG21	M20	10
166-51027	CNV-M25-PG21	PG21	M25	10
166-51028	CNV-PG16-PG21	PG21	PG16	10
166-51029	CNV-PG29-PG21	PG21	PG29	2
166-51030	CNV-M40-PG29	PG29	M40	1
166-51031	CNV-PG21-PG29	PG29	PG21	2
166-51032	CNV-PG36-PG29	PG29	PG36	2
166-51033	CNV-M50-PG36	PG36	M50	1
166-51034	CNV-PG29-PG36	PG36	PG29	2
166-51035	CNV-PG42-PG36	PG36	PG42	2
166-51000	CNV-M16-PG7	PG7	M16	10
166-51001	CNV-M20-PG7	PG7	M20	10
166-51002	CNV-PG9-PG7	PG7	PG9	10
166-51003	CNV-PG11-PG7	PG7	PG11	10
166-51004	CNV-PG13-PG7	PG7	PG13.5	10
166-51005	CNV-PG16-PG7	PG7	PG16	10
166-51006	CNV-M16-PG9	PG9	M16	10
166-51007	CNV-M20-PG9	PG9	M20	10
166-51008	CNV-PG7-PG9	PG9	PG7	10
166-51009	CNV-PG11-PG9	PG9	PG11	10
166-51010	CNV-PG13-PG9	PG9	PG13.5	10
166-51011	CNV-PG16-PG9	PG9	PG16	10

All dimensions in mm. Subject to technical changes.

• PAEC End Caps for Corrugated Conduits

Features and Benefits

- Snaps over end of conduit when not terminated with fitting
- Provides smooth entry to prevent damage to cables



HelaGuard PAEC End Cap.

Technical Table

Article-No.	Type	Conduit Ø	Pack Cont.
166-50800	PAEC16	16	10
166-50801	PAEC21	21	10
166-50802	PAEC28	28	10
166-50803	PAEC34	34	10
166-50804	PAEC42	42	10
166-50805	PAEC54	54	10

All dimensions in mm. Subject to technical changes.

Material Data

Material	Polyamide 6.6 (PA66)
Colour	Black (BK)
Operating Temperature	-50 °C to +135 °C

