




















Accessories for PMS to PHV 62X

	Rigid Tip 0.8 mm Order No. 018-291-011
	Spring Contact Tip gold plated 0.8 mm Order No. 018-594-803
	Spring Contact Tip gold plated 0.38 mm Order No. 890-101-380
	Rigid Tip gold plated 30 mm long Order No. 018-291-012
	Spring Contact Tip gold plated shape E Order No. 018-594-806
	Spring Contact Tip gold plated shape H Order No. 018-594-808
	Spring Contact Tip gold plated shape K Order No. 018-594-809
	Spring Contact Tip gold plated shape F Order No. 018-594-811
	Spring Contact Tip gold plated shape D Order No. 018-594-805
	Spring Contact Tip gold plated shape C Order No. 018-594-804
	Spring Contact Tip gold plated shape G Order No. 018-594-810


	Sprung hook II long black 890-320-000 red 890-320-020
	BNC adapter for probes Order No. 018-210-001
	Ground spring Order No. 890-400-003
	Coaxial PCB adapter Order No. 890-700-000
	Insulating cap Order No. 018-292-*17 * 0, 2, 4, 5
	IC Insulating cap Order No. 018-292-*16 * 0, 2, 4, 5
	Safety Alligator Clip Order No. 694-226-00* * 0, 2, 4, 5, 6
	Mini Hook™, 10 Colours Order No. Xr25-* Order No. XR25-S (Set 10 colours)
	Micro-Hook®, 10 Colours Order No. Xm25-* Order No. XM25-S (Set 10 colours)
	Double-Gripper, 10 Colours Order No. XKM-* Order No. XKM-S (Set 10 colours)
	Pico Hook™, 10 Colours Order No. P25-* Best.-Nr. P25-S (Set 10 colours)
	QFP IC-Clip pair long Order No. 890-502-130
	QFP IC-Clip pair short Order No. 890-502-000
	Extension lead with 0.8 mm socket 10 cm (4 in.) 890-600-200 5 cm (2 in.) 890-600-100
	Probe Adapter to Mini-Alligator Clip Order No. 890-50M-K00
	Probe Adapter to Mini-Clip Order No. 890-235-100
	Probe Adapter to Micro hook Order No. 890-23K-100
	Flexible Adapter 2 mm banana plug Order No. 890-202-000
	Flexible Adapter 4 mm banana plug Order No. 890-210-00* * 0, 2, 4, 5, 6
	Flexible Adapter 4 mm safety banana plug Order No. 890-320-000 Order No. 890-210-020
	Single Adapter lead to one 0.8 mm socket Best.-Nr. 890-510-700
	Dual Adapter lead to two 0.8 mm socket Best.-Nr. 890-520-701

*Colour Code:
1 = brown, 2 = red, 3 = orange, 4 = yellow, 5 = green,
6 = blue, 7 = violet, 8 = gray, 9 = white, 0 = black


Accessories

Universal Probe Kit black ZUB-U-SW 891-100-201
 Universal Probe Kit red ZUB-U-RT 891-102-201


Contains:
 Sprung hook II black or red, Insulating-cap, IC-cap, BNC adapter,
 Ground lead 22cm (8.6 in.)
 Rigid Tip 0.8 mm, Spring Tip 0.8mm and Trimmer Tool.




Ground lead
 with Mini Clip
 11 cm (4.3 in.) 890-400-011
 15 cm (6.0 in.) 890-400-016




HF-compensated
 Ground lead with
 Mini Alligator Clip
 22 cm (8.6 in.) 890-450-000




Standard Ground lead
 with Mini Alligator Clip
 11 cm (4.3 in.) 890-400-001
 15 cm (6.0 in.) 890-400-015
 22 cm (8.6 in.) 890-400-000
 30 cm (12.0 in.) 890-400-002




Adjustment Trimmer Tool
 Order No. 018-292-006




Adjustment Trimmer Tool with metal
 Order No. 018-292-007




Ground lead
 with 0.8 socket
 11 cm (4.3 in.) 890-400-013
 15 cm (6.0 in.) 890-400-018




Ground lead with
 2 mm banana plug
 22 cm (12.0 in.) 890-400-102



Ground lead with
 4 mm banana plug
 22 cm (12.0 in.) 890-400-104



Ground lead with
 4 mm safety
 banana plug
 22 cm (12.0 in.) 890-400-22x




Ground lead with 4 mm
 retractable banana plug
 22 cm (12.0 in.) 890-400-22R

Accessories and options for all PMK Probes

Set of 18 cable code rings,
 9 colours 2 of each Order No. 890-010-918
 Precision adjustment tool Order No. 018-292-024

Read Out option for PMK Probes:
 x10/x50/x100/x1000
 Can be mounted anytime except for series PMS
 Indicate Probe type only, when ordering.



Safety Alligator Clip
 Order No. 694-226-00*
 * 0, 2, 4, 5, 6