









LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN I APVD
DF	F0	C	REV PER	ECO-08-020844+6	06NOV08	PY BW

D

C

B

A



- 1. MILITARY PART NO., 00779, DATE CODE, PART NO. AND AMP MARKED THIS SIDE.
- 2. HOUSING MAT'L: POLYPHENYLENE SULFIDE, GST-40F PER MIL-M-24519.
- 3. CONTACT MAT'L: BRASS PER QQ-B-626.
- 4. CONTACT FINISH: .000050" [0.00127] GOLD OVER .000050" [0.00127] NICKEL IN CONTACT AREA.
- 5. CONTACT FINISH: .000100" [0.00254] TIN-LEAD OVER .000050" [0.00127] NICKEL
- 6. LETTERS INDICATING OUTSIDE ROWS AND NUMBERS INDICATING END CAVITIES (ROW C ONLY) MARKED ON THIS SURFACE.
- 7. NUMBERS INDICATING EVERY FIVE CAVITIES MARKED, BOTH SIDES.
- 8. MEETS ALL REQUIREMENTS OF MIL-C-55302.
- 9. LINES INDICATING EVERY FIVE CAVITIES MARKED ON MATING FACE EXCEPT END CAVITIES STARTING FROM POSN. #1.

M55302-129-08	240	IV	240	447207-8
M55302-129-07	240	III	240	447207-7
M55302-129-06	240	II	240	447207-6
M55302-129-05	240	I	240	447207-5
M55302-129-04	160	IV	240	447207-4
M55302-129-03	160	III	240	447207-3
M55302-129-02	160	II	240	447207-2
M55302-129-01	160	I	240	447207-1
MILITARY P/N	NO. OF CONTACTS	TYPE	NO. OF POSN	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C.THOMAS 5-4-90	 Tyco Electronics Corporation Harrisburg, PA 17105-3608	
		CHK D.MILLER 5-25-90		
DIMENSIONS: INCHES		NAME	PIN HEADER ASS'Y, RIGHT	
		PRODUCT SPEC	ANGLE, .100	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC	—	
0 PLC ± —		—	SIZE	
1 PLC ± —		—	CAGE CODE	
2 PLC ± —		—	DRAWING NO	
3 PLC ± .005 [0.13]		—	RESTRICTED TO	
4 PLC ± —		—	A1 00779 C 447207	
ANGLES ± —		WEIGHT	—	
FINISH		CUSTOMER DRAWING	SCALE 4:1 SHEET 1 OF 1 REV C	
				
				