




Compact EI Transformers SI-DIN 35

The standard molded 1 phase EI transformers with integrated screw terminals and DIN rail TS35 mount designed according to the following specifications.

- Designed for continuous load
- 3-module-enclosure
- High quality safety and isolating transformers designed for use in general applications. It could be also use for: bells, gongs and door openers.
- Standard primary winding 230VAC
- Detailed product specification on permanent label
- High efficiency, low regulation design
- 100% electrical and flash tested
- Thermal protection 100°C
- Protected against short circuit

Specifications:

Power: 8 - 20 VA
Frequency: 50/60 Hz
Primary: 230 VAC
Secondary: 2x4V, 8V, 2x12V
Isolation: 4 kV RMS
Temp. class: B (130°)
Standard: EN61558-2-6



Primary 230V, 8VA

Secondary	Type designation
2x4V	7720710
8V	7720701
2X12V	7720708

Primary 230V, 16VA

Secondary	Type designation
2x4V	7720717
2x12V	7720704



DATA SUPPORT

Schematics:

