



LOC	DIST	REVISIONS				
G	14	P	LTR	DESCRIPTION	DATE	OWN
			C2	REVISED PER ECO-11-005027	11MAR11	RK
		APVD				HMR



AMP
WIRE RANGE

8 AWG
SOLID OR STRANDED

- 1 STAMP AMP 8* APPROX AS SHOWN
- 2 COPPER PER ASTM B-152, ANNEALED
- 3 NICKEL PLATE 0.00762 [$.000300$] MIN THK PER QQ-N-290



323167
PART NO.

MAX RECOMMENDED OPERATING TEMPERATURE: 343°C MAX	THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TA BRINKMAN 4-19-93	 TE Connectivity			
			CHK DA PATTERSON 4-19-93				
VOLTAGE RATING: N/A	DIMENSIONS: mm[INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD JL MECKLEY 4-19-93	NAME		TERMINAL, RING TONGUE, HEAT RESISTANT, STRATO-THERM	
CIRCULAR MIL AREA: 6.64-10.5mm² [13,100-20,800] SOLID OR STRANDED		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± ± - FINISH	PRODUCT SPEC — APPLICATION SPEC — WEIGHT —	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
		MATERIAL - 	- 	A2	00779	 323167	—
		CUSTOMER DRAWING		SCALE 4:1	SHEET 1 of 1	REV C2	