


DRAWING MADE IN THIRD ANGLE PROJECTION

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION


© COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE COVERED BY U. S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.

MOD 20 LOC BD DIST 39

REVISIONS					
P	F	ZONE	LTR	DESCRIPTION	DATE
			O	RELEASED	
			O	REVISED ECN-0048	4-10-84
			A	REV PER ECN BD2622	2-10-85
			B	REV PER ECN BD4356	9-20-85



- CONNECTORS COMPLY WITH AMP SPEC. 108-40,012 AND MATE WITH ANY SAME NUMBER POSITION RECEPTACLE CONNECTOR IN AMPLIMITE SERIES.
- CONNECTOR DESIGNED FOR 28 AND 26 AWG STRANDED AND SOLID CONDUCTOR RIBBON CABLE ON .050¢.
- DIMENSION APPLIES TO TERMINATED CONNECTOR.
- MOLDED PARTS: FLAME RETARDANT 94V-0 RATED THERMOPLASTIC, COLOR: BLACK.
- STEEL PER QQ-S-698.
- PHOS. BRONZE PER QQ-B-750.
- GOLD PLATING PER MIL-G-45204, BRIGHT TIN PLATING PER MIL-T-10727 (NOT TIN LEAD), NICKEL PLATING PER QQ-N-290.
- BRIGHT TIN PLATED.
- .000030 GOLD ON MATING END, .000100-.000200 BRIGHT TIN OR BRIGHT TIN LEAD ON TERMINATION END, ALL OVER .000050 NICKEL ON ENTIRE CONTACT.



1.216	.984	.759	.666	.400	8	9	747306-4
1.541	1.312	1.087	.994	.700	14	15	747306-3
2.090	1.852	1.623	1.534	1.200	24	25	747306-2
2.732	2.500	2.275	2.183	1.800	36	37	747306-1
F	E	D	C	B	A	NO. OF POS.	PART NUMBER

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON: DECIMALS ± .005 ANGLES ± 2°		CONTRACT NO		AMP INCORPORATED Harrisburg, Pa.	
MATERIAL MOLDED PARTS: △ SHELL: △ CONTACTS: △		DR J. GERACE 9-15-83 CHK J. GERACE 9-15-83 APPD D. HOFFMAN 9-23-83 APPD T. LYZINSKI 9-29-83		NAME PLUG ASSEMBLY, LOW PROFILE HDF, FRONT METAL SHELL, W/ PREASSEMBLED COVER	
FINISH △ SHELL: △ CONTACTS: △		DSGN APPD OTHER APPD		SIZE C FSCH NO 00779 DRAWING NO 747306	
				SCALE - SHEET -	

AMP 1471-6 REV 2-81

20 SEP 1990 06:45:31 AMP100

CUSTOMER DRAWING