

PC20BU/HS1
PC20BU/HS4



Standard Schalterkonfiguration

ON

OFF

0 deg CW

Rotation

300 deg CW

215°
CCW

Top View Dimensions:
 - Overall width: 20.40
 - Inner width: 17.00
 - Central width: 8.80
 - Total height: 25.20
 - Distance from top to terminal row: 15.00
 - Distance between terminal rows: 5.00
 - Terminal width: 1.10 x 0.45
 - Distance from terminal row to bottom: 4.00
 - Side height: 17.00

Side View Dimensions:
 - Top width: 19.00
 - Distance from top to terminal row: 9.50
 - Distance from terminal row to bottom: 10.00
 - Distance from bottom to terminal row: 3.90
 - Distance from terminal row to side: 1.10 x 0.65
 - Side height: 6.00
 - Distance from top to side: 19.00 ± 0.5
 - Side width: 7.00
 - Distance from side to terminal row: 12.00
 - Distance from side to bottom: 10.00
 - Side width: 10.00
 - Side width: 4.60 x 10.00 LG
 - Side width: 6.00

Track Pinout View Dimensions:
 - Distance between terminals: 10.00
 - Distance from terminal to side: 5.00
 - Distance from terminal to side: 5.00
 - Distance from terminal to side: 1.30 DIA
 - Distance from terminal to side: 10.00
 - Distance from terminal to side: 9.10
 - Distance from terminal to side: 10.20

SWITCH TERMINALS 1,1

1.30 DIA

TRACK PINOUT
VIEWED ON COMPONENT SIDE