

4

3

2

1




LOC	DIST	REVISIONS				
P	LTR	DESCRIPTION			DATE	APVD
		REVISED PER ECO-11-004917			11MAR11	RK HMR

SPECIFICATIONS:


MATERIALS:
HOUSING: POLYAMIDE, (BLACK) UL94-0
TERMINALS: COPPER ALLOY, TIN PLATE
SCREWS:ZINC PLATED STEEL WITH CLEAR CHROMATE COATING

ELECTRICAL:
RATING: 25A 300V
WIRE RANGE: 12 – 22 AWG

MECHANICAL:
MAXIMUM TORQUE RATING: 7 IN.-LBS.



10.875	11.311	28	6STR-28-008	2-1546242-8
10.500	10.936	27	6STR-27-008	2-1546242-7
10.125	10.561	26	6STR-26-008	2-1546242-6
9.750	10.186	25	6STR-25-008	2-1546242-5
9.375	9.811	24	6STR-24-008	2-1546242-4
9.000	9.436	23	6STR-23-008	2-1546242-3
8.625	9.061	22	6STR-22-008	2-1546242-2
8.250	8.686	21	6STR-21-008	2-1546242-1
7.875	8.311	20	6STR-20-008	2-1546242-0
7.500	7.936	19	6STR-19-008	1-1546242-9
7.125	7.561	18	6STR-18-008	1-1546242-8
6.750	7.186	17	6STR-17-008	1-1546242-7
6.375	6.811	16	6STR-16-008	1-1546242-6
6.000	6.436	15	6STR-15-008	1-1546242-5
5.625	6.061	14	6STR-14-008	1-1546242-4
5.250	5.686	13	6STR-13-008	1-1546242-3
4.875	5.311	12	6STR-12-008	1-1546242-2
4.500	4.936	11	6STR-11-008	1-1546242-1
4.125	4.561	10	6STR-10-008	1-1546242-0
3.750	4.186	9	6STR-09-008	1546242-9
3.375	3.811	8	6STR-08-008	7-1437654-2
3.000	3.436	7	6STR-07-008	796988-7
2.625	3.061	6	6STR-06-008	1546242-6
2.250	2.686	5	6STR-05-008	9-1546158-4
1.875	2.311	4	6STR-04-008	1546242-4
1.500	1.936	3	6STR-03-008	796988-6
1.125	1.561	2	6STR-02-008	8-1546158-9
DIM B	DIM A	NO. OF POS.	BUCHANAN PART NO.	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN E. ZANOLINI 04FEB2002	 TE Connectivity	
DIMENSIONS: INCHES		CHK S. YODER 04FEB02		
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± .01 3 PLC ± .005 4 PLC ± - ANGLES ± 1/2	APVD S. YODER 04FEB02	NAME	
		PRODUCT SPEC	6STR-XX-008	
		APPLICATION SPEC	SIZE CAGE CODE DRAWING NO RESTRICTED TO	
MATERIAL	FINISH	WEIGHT	A300779C-7-1437654-2	
CUSTOMER DRAWING			SCALE NTS	SHEET 1 OF 1 REV D1