





ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

SPC-F005.DWG

REVISIONS

DOC. NO. SPC-F005 * Effective: 7/8/02 * DCP No: 1398

DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
2091	A	RELEASED	JYC	4/7/10	JYC	4/7/10	JYC	4/7/10



Material: Nylon, Carbonate A added for greater resistance to ultra violet light

Part Number		Length		Width		Max. Bundle Dia		Min. Tensile Strength
100 pcs	1000 pcs	m.m.	inch	m.m.	Inch	m.m.		lbs(kgs)
SPC35258	SPC35288	75	3	2.4	.093	15	0.591	18 (8)
SPC35259	SPC35289	100	4	2.5	.093	22	0.866	18 (8)
SPC35264	SPC35290	120	4.75	2.5	.093	28	1.100	18 (8)
SPC35260	SPC35291	142	5.5	2.5	.093	35	1.378	18 (8)
SPC35261	SPC35292	165	6.5	2.5	.093	43	1.693	18 (8)
SPC35262	SPC35293	203	8	2.5	.093	55	2.165	18 (8)
SPC35263	N/A	400	15.75	2.5	.093	116	4.567	18 (8)
SPC35264	N/A	120	4.75	3.2	.125	27	1.063	40 (18)
SPC35265	SPC35294	142	5.5	3.2	.125	34	1.339	40 (18)
SPC35266	SPC35295	150	6	3.6	.141	36	1.417	40 (18)
SPC35267	SPC35296	180	7	3.6	.141	46	1.811	40 (18)
SPC35268	SPC35297	203	8	3.2	.125	53	2.087	40 (18)
SPC35269	SPC35298	250	10	3.6	.141	68	2.677	40 (18)
SPC35270	SPC35299	265	10.5	3.6	.141	68	2.670	40 (18)
SPC35271	SPC35300	292	11.5	3.6	.141	82	3.228	40 (18)
SPC35272	N/A	330	13	3.6	.141	93	3.661	40 (18)
SPC35273	N/A	368	14.5	3.6	.141	105	4.134	40 (18)
SPC35274	SPC35301	120	4.75	4.8	.187	22	0.866	50 (22)
SPC35275	SPC35302	160	6.5	4.8	.187	39	1.535	50 (22)
SPC35276	SPC35303	190	7.5	4.8	.187	49	1.929	50 (22)
SPC35277	SPC35304	203	8	4.6	.187	52	2.047	50 (22)
SPC35278	SPC35305	250	10	4.8	.187	68	2.677	50 (22)
SPC35279	SPC35306	280	11	4.8	.187	77	3.031	50 (22)
SPC35280	N/A	310	12	4.8	.187	86	3.386	50 (22)
SPC35281	N/A	368	14.5	4.8	.187	105	4.134	50 (22)
SPC35282	N/A	450	17.75	4.8	.187	131	5.157	50 (22)
SPC35283	SPC35307	203	8	7.6	.297	52	2.047	120 (55)
SPC35284	SPC35308	240	9.437	7.6	.297	61	2.402	120 (55)
SPC35285	N/A	300	11.875	7.6	.297	80	3.150	120 (55)
SPC35286	N/A	340	13.5	7.6	.297	92	3.622	120 (55)
SPC35287	N/A	380	15	7.6	.297	105	4.134	120 (55)

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:	DATE:
JYC	4/7/2010
CHECKED BY:	DATE:
JYC	4/7/2010
APPROVED BY:	DATE:
JYC	4/7/2010

DRAWING TITLE:			
Weather Resistant Ties (Black)			
SIZE	DWG. NO.	ELECTRONIC FILE	REV
A	TA-1224	TA-1224.dwg	A
SCALE: NTS		U.O.M.: mm [INCHES]	SHEET: 1 OF 1