

GENTECH INTERNATIONAL LTD

Grangestone Industrial Estate
Girvan, Ayrshire KA26 9PS
United Kingdom

Telephone: +44 1465 713581
Fax: +44 1465 714974

E-Mail: info@gentechsensors.com
Web Site www.gentechsensors.com

FLOW SWITCH

FS Series - Flow Switch in Copper

FS-10

Design Features

- 15mm copper pipe
- Minimal pressure drop
- Operates from a small head of water
- Vertical mount +/- 15°
- Suitable for water and air flow switching



Product Comments

- 15mm copper pipe
- Suitable for hot and cold portable water
- Reed Switch reliability
- Meets UL 94-HB flammability rating
- Easy installation

Typical Applications


- Mains water control
- Power Shower
- Central Heating Systems
- Leak Detection
- Cooling systems

Material, Design and Operation

Mounting:	Flow Switch Vertical
Material:	Copper
Fitting	Flow Switch 15mm pipe size
Contact Form:	Form A -SPST
Contact Material:	Ruthenium
Maximum Watts	15 Watts
Maximum Switching Volts:	300 VDC
Maximum Switching Current:	1.0A
Cable Type:	2 x 16/0.2mm PVC insulated 1.0M long
Cable Colour:	Black/Black
Operating Temperature Range:	85 °C
Medium/Liquid:	Water
Flow Rate:	0.5 litres/min
Operating Pressure:	10BAR
Mounting Shock:	50g for 11ms duration
Mounting Vibration:	35g up to 500Hz

Line Drawing

FS-10



Installation

- Pipework to be cut square and burr free
- Compression fitting mating connectors to be of suitable quality.
- The installation should be checked to ensure that no leaking is evident.
- Pipework/connector alignment imperative (avoiding bending stress).

Flow Rate v Pressure Drop

