


Type: **DILA-40(24V50HZ)**  
Article No.: **276316**



#### Ordering information


|                                                   |          |   |                |
|---------------------------------------------------|----------|---|----------------|
| Rated operational current AC-15 220 V 230 V 240 V | $I_e$    | A | 6              |
| Rated operational current AC-15 380 V 400 V 415 V | $I_e$    | A | 4              |
| Conventional current, open at 60 °C               | $I_{th}$ | A | 10             |
| Can be combined with auxiliary contact module     |          |   | DILA-XHI(V)... |

#### Contact sequence




#### Notes concerning the product group

*With screw terminals:*



| <i>Accessories</i>         | <i>Page</i> |
|----------------------------|-------------|
| 1 Suppressor               | → 281208    |
| 2 Auxiliary contact module | → 276420    |
| Further actuating voltages | → 276315    |

*With springloaded terminals:*



| <i>Accessories</i>         | <i>Page</i> |
|----------------------------|-------------|
| 1 Suppressor               | → 281208    |
| 2 Auxiliary contact module | → 276420    |
| Further actuating voltages | → 276315    |

Contact numbers to EN 50011

Coil terminal markings to EN 50005

DC operated contactor relays have a built-in suppressor circuit.

## Contacts

|                           |       |   |   |
|---------------------------|-------|---|---|
| Rated operational current |       |   |   |
| AC-15                     |       |   |   |
| 220/240 V                 | $I_e$ | A | 6 |
| 380/415 V                 | $I_e$ | A | 4 |

Moeller GmbH, Hein-Moeller-Str. 7-11, D-53115 Bonn  
E-Mail: [catalog@moeller.net](mailto:catalog@moeller.net), Internet: [www.moeller.net](http://www.moeller.net), <http://catalog.moeller.net>  
Copyright 2005 by Moeller GmbH. Subject to modifications. HPL-C2005GB-INT V3.0