


HC-M-PN3-MOD-ST-BU

Order No.: 1663475



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1663475>

HEAVYCON pneumatic module, male/female, 3 connections

Commercial data

GTIN (EAN)	 4 017918 123284
sales group	D042
Pack	2 pcs.
Customs tariff	85369010
Catalog page information	Page 462 (PC-2009)

Product notes

WEEE/RoHS-compliant since:
10/30/2006



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

Electrical characteristics

Note	Hinged retaining frame HC-M-MHR...is required for HEAVYCON-ADVANCE housing of types B6 to B24 and HEAVYCON housing of types B6 to B48, pneumatic HC-M-PN... male and female connectors (Pneumatic male and female connectors not included in the scope of supply)
Ambient temperature (operation)	-40 °C ... 80 °C
Number of positions	3

Mechanical characteristics

Internal diameter of pressure hose connection	4 mm
Insertion/withdrawal cycles	≥ 500

General characteristics

Color	blue
Number of module slots	1
Inflammability class acc. to UL 94	V0
Assembly instructions	Housing height ≥ 52 mm. Use of HC-CST (1676857) coding pins and HC-CBU (1676860) coding sockets has been prescribed. Observe the min bending radii when connecting the tubes.

Material data

Contact carrier material	PC
--------------------------	----

Certificates / Approvals




Certification

CSA, GOST, UL

Diagrams/Drawings

Dimensioned drawing



3-pos.

Address

PHOENIX CONTACT Deutschland GmbH
Flachsmarktstr. 8
32825 Blomberg, Germany
Phone +49 5235 3 12000
Fax +49 5235 3 41200
<http://www.phoenixcontact.de>



© 2010 Phoenix Contact
Technical modifications reserved;