


Fuses and Fuse Holders

5 × 20 mm Fuses — Low and High Breaking Capacity



According to IEC 127, rated 250 V. **Type FSF**, UL recognized, CSA accepted 32 mA-10 A, SEMKO, VDE, BEAB approved 32 mA-6.3 A. **Type FST**, UL recognized, CSA accepted 32 mA-16 A; BSI approved 125 mA-6.3 A; CB, BEAB, SEMKO, VDE approved 32 mA-6.3 A. **Breaking Capacity**: 35 A/250 V. **Type SP**, UL recognized, CSA accepted 500 mA-16 A, VDE, SEMKO, SEV approved 500 mA-6.3 A. **Type SPT**, UL recognized, CSA accepted 500 mA-16 A VDE, SEMKO, SEV approved 1 A-6.3 A. **Types FSU and SSU**. Meet UL 1459; GR1089; ITU-TK.20 for telecom applications. Pigtailed fuses are available as special orders.

| Amps   | Fast Type FSF |             |       | Time Delay Type FST |             |       |
|--------|---------------|-------------|-------|---------------------|-------------|-------|
|        | Stock No.     | Mfr.'s Type | EACH* | Stock No.           | Mfr.'s Type | EACH* |
| 100 mA | 798-0076      | 0034.1506   | .50   | 798-0112            | 0034.3107   | .57   |
| 125 mA | 798-0078      | 0034.1507   | .50   | 798-0114            | 0034.3108   | .57   |
| 160 mA | 798-0080      | 0034.1508   | .50   | 798-0116            | 0034.3109   | .57   |
| 200 mA | 798-0082      | 0034.1509   | .50   | 798-0118            | 0034.3110   | .57   |
| 250 mA | 798-0084      | 0034.1510   | .50   | 798-0120            | 0034.3111   | .57   |
| 315 mA | 798-0086      | 0034.1511   | .50   | 798-0122            | 0034.3112   | .57   |
| 400 mA | 798-0088      | 0034.1512   | .50   | 798-0124            | 0034.3113   | .57   |
| 500 mA | 798-0090      | 0034.1513   | .50   | 798-0126            | 0034.3114   | .51   |
| 630 mA | 798-0092      | 0034.1514   | .50   | 798-0128            | 0034.3115   | .51   |
| 800 mA | 798-0094      | 0034.1515   | .50   | 798-0130            | 0034.3116   | .51   |
| 1 A    | 798-0096      | 0034.1516   | .50   | 798-0132            | 0034.3117   | .51   |
| 1.25 A | 798-0098      | 0034.1517   | .50   | 798-0134            | 0034.3118   | .51   |
| 1.6 A  | 798-0099      | 0034.1518   | .50   | 798-0136            | 0034.3119   | .51   |
| 2 A    | 798-0100      | 0034.1519   | .50   | 798-0138            | 0034.3120   | .51   |
| 2.5 A  | 798-0102      | 0034.1520   | .50   | 798-0140            | 0034.3121   | .51   |
| 3.15 A | 798-0104      | 0034.1521   | .50   | 798-0142            | 0034.3122   | .51   |
| 4 A    | 798-0106      | 0034.1522   | .50   | 798-0144            | 0034.3123   | .51   |
| 5 A    | 798-0108      | 0034.1523   | .50   | 798-0146            | 0034.3124   | .27   |
| 6.3 A  | 798-0110      | 0034.1524   | .50   | 798-0148            | 0034.3125   | .54   |

\*Sold in multiples of 5 only. For larger quantity price breaks, contact your local Allied sales representative.

| Amps   | Time Delay Type FSU |             |       |
|--------|---------------------|-------------|-------|
|        | Stock No.           | Mfr.'s Type | EACH* |
| 250 mA | 798-0900            | 2010.0011   | .52   |
| 400 mA | 798-0904            | 2010.0013   | .52   |
| 500 mA | 798-0906            | 2010.0014   | .52   |
| 630 mA | 798-0908            | 2010.0015   | .52   |
| 1 A    | 798-0912            | 2010.0017   | .52   |
| 1.25 A | 798-0914            | 2010.0018   | .52   |
| 1.6 A  | 798-0918            | 2010.0019   | .52   |
| 2 A    | 798-0920            | 2010.0020   | .52   |
| 2.5 A  | 798-0922            | 2010.0021   | .52   |
| 3.15 A | 798-0924            | 2010.0022   | .52   |

\*Sold in multiples of 5 only. For larger quantity price breaks, contact your local Allied sales representative.

| Amps   | Fast Type SP |             |       | Time Delay Type SPT |             |       |
|--------|--------------|-------------|-------|---------------------|-------------|-------|
|        | Stock No.    | Mfr.'s Type | EACH* | Stock No.           | Mfr.'s Type | EACH* |
| 500 mA | 798-0150     | 0001.1001   | .85   | 798-0926            | 0001.2501   | 2.00  |
| 630 mA | 798-0152     | 0001.1002   | .85   | 798-0928            | 0001.2502   | 2.00  |
| 800 mA | 798-0154     | 0001.1003   | .85   | —                   | —           | —     |
| 1 A    | 798-0156     | 0001.1004   | .85   | 798-0932            | 0001.2504   | 2.00  |
| 1.25 A | 798-0158     | 0001.1005   | .85   | 798-0934            | 0001.2505   | 2.00  |
| 1.6 A  | 798-0160     | 0001.1006   | .85   | —                   | —           | —     |
| 2 A    | 798-0162     | 0001.1007   | .85   | 798-0938            | 0001.2507   | 2.00  |
| 2.5 A  | 798-0164     | 0001.1008   | .85   | 798-0940            | 0001.2508   | 2.00  |
| 3.15 A | 798-0166     | 0001.1009   | .85   | 798-0942            | 0001.2509   | 2.00  |
| 4 A    | 798-0168     | 0001.1010   | .85   | 798-0944            | 0001.2510   | 2.26  |
| 5 A    | 798-0170     | 0001.1011   | .85   | 798-0946            | 0001.2511   | 2.00  |
| 6.3 A  | 798-0172     | 0001.1012   | .85   | 798-0948            | 0001.2512   | 2.00  |


\*Sold in multiples of 5 only. For larger quantity price breaks, contact your local Allied sales representative.

| Amps   | Fast Type SSU |             |       |
|--------|---------------|-------------|-------|
|        | Stock No.     | Mfr.'s Type | EACH* |
| 630 mA | 798-0952      | 2020.0002   | 1.28  |
| 1 A    | 798-0956      | 2020.0004   | 1.28  |
| 2 A    | 798-0962      | 2020.0007   | 1.28  |
| 2.5 A  | 798-0964      | 2020.0008   | 1.28  |
| 3.15 A | 798-0966      | 2020.0009   | 1.28  |

\*Sold in multiples of 5 only. For larger quantity price breaks, contact your local Allied sales representative.

Turn To Section 1 For Allied Office Addresses and Local Phone Numbers


5 × 20 mm Fuseholders



Fuseholders for 5 × 20 mm fuses according to IEC 257, UL 512. All UL recognized, CSA certified, VDE, SEMKO and SEV approved at 250 V. Panel mount styles have solder/quick-disconnect terminals. Various mounting styles for panel or PCB. IP 67 models are watertight.

| Stock No. | Mfr.'s Type | Fig. | Fuse Carrier       | Terminals | Panel Mounting | EACH |
|-----------|-------------|------|--------------------|-----------|----------------|------|
| 798-0019  | 3101.0010   | 1    | Slotted            | Solder    | Front          | 2.30 |
| 798-0017  | 3101.0015   | 1    | Finger Grip        | Solder    | Front          | 2.30 |
| 798-0015  | 3101.0110   | 1    | Slotted, IP 67     | Solder    | Front          | 2.57 |
| 798-0542  | 3101.0115   | 1    | Finger Grip, IP 67 | Solder    | Front          | 2.50 |
| 798-0544  | 3101.0020   | 2    | Slotted            | Solder    | Rear           | 2.30 |
| 798-0546  | 3101.0025   | 2    | Finger Grip        | Solder    | Rear           | 2.30 |
| 798-0548  | 3101.0120   | 2    | Slotted, IP 67     | Solder    | Rear           | 2.57 |
| 798-0013  | 3101.0040   | 3    | Slotted            | PCB       | PCB            | 2.30 |
| 798-0552  | 3101.0045   | 3    | Finger Grip        | PCB       | PCB            | 2.30 |
| 798-0011  | 3101.0050   | 4    | Slotted            | PCB       | PCB            | 2.30 |
| 798-0554  | 3101.0055   | 4    | Finger Grip        | PCB       | PCB            | 2.30 |
| 798-0021  | 3101.0030   | 5    | Slotted            | Solder    | Snap-in        | 2.30 |
| 798-0556  | 3101.0035   | 5    | Finger Grip        | Solder    | Snap-in        | 2.24 |
| 798-0558  | 3101.0031   | 5    | Slotted            | Solder    | Snap-in        | 2.30 |

International Fuseholders




Fuseholders for 5 × 20 mm or 1/4" × 1 1/4" fuses according to IEC 257, UL 512. All UL recognized; CSA certified, VDE, SEMKO, and SEV approved at 250 V. Various mounting styles for panel or PCB. All fuseholders complete with carriers except type FUL, ordered separately. IP 67 models are watertight.

| Stock No. | Mfr.'s Type | Fig. | Fuse Carrier               | Terminals        | Panel Mounting         | EACH |
|-----------|-------------|------|----------------------------|------------------|------------------------|------|
| 798-0570  | 0031.1706   | 1    | Slotted, 5 × 20 mm         | Solder           | Screw-on, low profile  | 1.86 |
| 798-0572  | 0031.1699   | 1    | Slotted, 1/4" × 1 1/4"     | Solder           | Screw-on, low profile  | 1.83 |
| 798-0574  | 0031.1803   | 1    | Finger Grip, 5 × 20 mm     | Quick disconnect | Screw-on, low profile  | 2.38 |
| 798-0576  | 0031.1804   | 1    | Finger Grip, 1/4" × 1 1/4" | Quick disconnect | Screw-on, low profile  | 2.63 |
| 798-0578  | 0031.1767   | 1    | Slotted, 5 × 20 mm         | Quick connect    | Screw-on, high profile | 1.80 |
| 798-0580  | 0031.1768   | 1    | Slotted, 1/4" × 1 1/4"     | Quick connect    | Screw-on, high profile | 1.78 |

| Stock No. | Mfr.'s Type | Fig. | Fuse Carrier           | Terminals | Panel Mounting    | EACH |
|-----------|-------------|------|------------------------|-----------|-------------------|------|
| 798-0582  | 0031.3821   | 2    | Slotted, 5 × 20 mm     | PCB       | PCB, high profile | 2.10 |
| 798-0584  | 0031.3822   | 2    | Slotted, 1/4" × 1 1/4" | PCB       | PCB, high profile | 2.08 |
| 798-0586  | 0031.3571   | 3    | Slotted, 5 × 20 mm     | PCB       | PCB, high profile | 1.87 |
| 798-0588  | 0031.3581   | 3    | Slotted, 1/4" × 1 1/4" | PCB       | PCB, high profile | 1.84 |

| Stock No. | Mfr.'s Type | Fig. | Fuse Carrier                  | Terminals        | Panel Mounting        | EACH |
|-----------|-------------|------|-------------------------------|------------------|-----------------------|------|
| 798-0590  | 0031.2303   | 4    | Holder Body Only, IP 67       | Solder           | Screw-on, low profile | 3.82 |
| 798-0592  | 0031.2308   | 4    | Holder Body Only              | Quick disconnect | Screw-on, low profile | 3.78 |
| 798-0594  | 0031.2320   | 4    | Carrier, 1/4" × 1 1/4", IP 67 | —                | —                     | 2.59 |
| 798-0596  | 0031.2321   | 4    | Carrier, 1/4" × 1 1/4", IP 40 | —                | —                     | 2.96 |
| 798-0598  | 0031.2322   | 4    | Carrier, 5 × 20 mm, IP 67     | —                | —                     | 3.43 |
| 798-0600  | 0031.2323   | 4    | Carrier, 5 × 20 mm, IP 40     | —                | —                     | 2.88 |

Open Design Fuse Clip/Blocks



Built according to IEC 257, UL 512. UL recognized, CSA certified, VDE, SEMKO, and SEV approved at 250 V. Fig. 4 available with cover. Figs. 3 and 5 accept 5 × 20 mm or 1/4" × 1 1/4" fuses, one fuse at a time per IEC 65. Kicked terminals for wave soldering. 0751.0099 is tin plated bronze. 0751.0100 is tin plated brass.

| Stock No. | Mfr.'s Type | Fig. | Fuse Size                  | Pin Spacing | EACH |
|-----------|-------------|------|----------------------------|-------------|------|
| 798-5050  | 0751.0110   | 1    | 5 × 20 mm                  | 5 mm        | .19  |
| 798-5051  | 0751.0052   | 2    | 5 × 20 mm                  | 5 mm        | .19  |
| 798-0045  | 0751.0099   | 3    | 5 × 20 mm or 1/4" × 1 1/4" | 5 mm        | .89  |
| 798-0042  | 0751.0100   | 3    | 5 × 20 mm or 1/4" × 1 1/4" | 5 mm        | .55  |
| 798-0362  | 0031.8201   | 4    | 5 × 20 mm                  | 22.5 mm     | .51  |
| 798-0364  | 0031.8211   | 4    | 5 × 20 mm                  | 25.0 mm     | .51  |
| 798-0366  | 0031.8221   | 4    | 5 × 20 mm                  | SMD         | .99  |
| 798-0536  | 0031.8231   | 5    | 5 × 20 mm or 1/4" × 1 1/4" | 5 mm        | .87  |