

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0982670242](#)  
**Status:** **Active**  
**Overview:** [Premo-Flex Cable Jumpers](#)  
**Description:** 1.00mm Pitch Premo-Flex FFC Jumper, Opposite Side Contacts (Type D), 254.00mm Cable Length, Tin (Sn) Plating, 8 Circuits

**Documents:**

[Drawing \(PDF\)](#) [Datasheet \(PDF\)](#)  
[Packaging Specification PK-98267-001-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family Cable  
 Series [98267](#)  
 Comments Contacts on opposite sides, Type D  
 Crimp Quality Equipment Yes  
 Overview [Premo-Flex Cable Jumpers](#)  
 Product Name Premo-Flex FFC Jumper  
 UPC 756054770726

**Physical**

Cable Length 254.00mm  
 Circuits (Loaded) 8  
 Material - Plating Mating Tin  
 Net Weight 1.503/g  
 Packaging Type Bag  
 Pitch - Mating Interface 1.00mm  
 Temperature Range - Operating -40° to +105°C  
 Wire Size AWG N/A  
 Wire/Cable Type Flat Flex Cable

**Electrical**

Current - Maximum per Contact 1.2A  
 Voltage - Maximum 60V AC

**Material Info**

**Reference - Drawing Numbers**

Packaging Specification PK-98267-001-001  
 Sales Drawing SD-98267-001



*Series image - Reference only*

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[98267 Series](#)

**Mates With**

Easy-On FFC/FPC Connector: <br>  
[522070833](#) , [522710879](#) , [526100833](#) ,  
[526100834](#)