




- 1 HOUSING: HIGH TEMPERATURE THERMOPLASTIC, COLOR NATURAL.
PIN CONTACTS: PHOSPHOR BRONZE.
GROUND BUSSES: PHOSPHOR BRONZE.
- 2 CONTACTS & GROUND BUSES: 0.00076(.000030) MIN. GOLD PER ASTM B 488 ON CONTACT AREA, 0.00254-0.00762(.000100-.000300) MATTE TIN PER ASTM B 545 ON SOLDER TAIL, ALL OVER 0.00127-0.00254(.000050-.000100) MATTE NICKEL PER SAE AMS-QQ-N-290 ON ENTIRE CONTACT.
- 3 DATE CODE MARKED IN AREA INDICATED.

125.73[4.950]	99	128.22[5.048]	130.68[5.145]	132.44[5.214]	200	5536272-9
113.03[4.450]	89	115.52[4.548]	117.98[4.645]	119.74[4.714]	180	5536272-8
100.33[3.950]	79	102.82[4.048]	105.28[4.145]	107.04[4.214]	160	5536272-7
87.63[3.450]	69	90.12[3.548]	92.58[3.645]	94.34[3.714]	140	5536272-6
OBSOLETE 74.93[2.950]	59	77.42[3.048]	79.88[3.145]	81.64[3.214]	120	5536272-5
62.23[2.450]	49	64.72[2.548]	67.18[2.645]	68.94[2.714]	100	5536272-4
OBSOLETE 49.53[1.950]	39	52.02[2.048]	54.48[2.145]	56.24[2.214]	80	5536272-3
36.83[1.450]	29	39.32[1.548]	41.78[1.645]	43.54[1.714]	60	5536272-2
24.13[.950]	19	26.62[1.048]	29.08[1.145]	30.84[1.214]	40	5536272-1
E	D	C	B	A	NO OF POS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A. FERNANDEZ CHK D. DIXON APVD D. DIXON	01-20-05 01-20-05 01-20-05	Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.13 [.005] 4 PLC ± - ANGLES ± -		PRODUCT SPEC 108-1272 APPLICATION SPEC 114-11005		PLUG ASSEMBLY, 10.92[.430] STACK, 3.18[.125] TAIL, BOARD TO BOARD, MICRO-STRIP	
MATERIAL 1		FINISH 2		SIZE A1	RESTRICTED TO
CUSTOMER DRAWING		SCALE 10:1		SHEET 1 OF 1 REV 03	