

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1200795010

Status:

Active

Overview:

Brad Ultra-Lock Connection System

Description:

Ultra-Lock (M12) Single-Ended Cordset, 12 Poles, Male (Straight) to Pigtail, 26 AWG, PUR Cable, 10.0m (32.81') Length



Series image - Reference only

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR6837

General

Product Family

Series

Connector End A

Connector End B

IP Rating

Material - Contact

Overview

Product Name

Protocol

Region

Type

UPC

Industrial Cordsets

120079

Ultra-Lock (M12)

Pigtail

IP67

Copper Alloy

Brad Ultra-Lock Connection System

Ultra-Lock (M12)

EtherNet

America

Single Ended

883906923839

Physical

Cable Diameter

Cable Length

Color - Cable Jacket

Coupling Style

Gender

Keyway

LED Indicator

Material - Cable Jacket

Material - Connector Body

Material - Coupling Nut

Material - O-Ring

Material - Plating Mating

Orientation

Poles

Temperature Range - Operating

Wire Size AWG

Wire/Cable Type

6.00mm (.236")

10.0m (32.81')

Yellow

Push to Lock

Male-Pigtail

Single

No

PUR

PUR

Nickel-plated Brass

Fluoro-elastomer

Gold

Straight to Pigtail

12

-25°C to +90°C

26

UL 20549

Electrical

Current - Maximum per Contact

Voltage - Maximum

1.5A

30V AC/DC

Material Info

Engineering Number

W0C006H45M100

Reference - Drawing Numbers

Sales Drawing

1200795006-000

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

120079 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION