



PUNCH-18.6MM PACKAGED (740-E)

Standard Slug-Splitter Knockout Punches

Cat No: 31119

UPC No: 783310311195

### Description

- Slug-Splitter SC heavy-duty punches are designed to punch up through 10 gauge (3.5 mm) stainless steel
- Unique slug-splitting design and tool steel construction easily punch 10 gauge (3.5 mm) mild steel and stainless steel
- Self-centering punch aligns itself on pilot hole. (Slug-Splitter SC)
- No need to draw crosshairs or line up die alignment marks
- (Slug-Splitter SC)
- Unique punch profile also splits slugs for easier slug removal
- Heavy-duty dies and stainless steel draw studs for longer life
- Excellent abrasion resistance for punching fiberglass and plastic
- Slug-Splitter SC punch units consist of: punch, die and draw stud
- Check individual punch for specific capacity
- U.S. Patent No. 4,543,722 for standard Slug-Splitter
- Patent Pending for Self-centering Slug-Splitter SC

### Specifications

- Application : For Standard Slug-Splitter Knockout Punches
- Capacity Stainless Steel : 12 GA (2.500 MM)
- Draw Studs :
  - 29451, 29451 Hydraulic Drivers
  - 30227 Ratchet Driver
- PG : 11
- Size : 0.732 IN (18.600 MM)
- Type : Knockout