




DIN 85 A

~ISO 1580

Standard withdrawn



BN 653

Slotted pan head machine screws

Stainless steel A4

- ~UNI 6108
- ~CSN 021137



All lengths fully threaded

M1,6; M2; M2,5: in accordance with ISO 1580

Article#	d ₁	d ₂	k	n	t min.	L
3646766	M1,6	3,2	1	0,4	0,35	3
3646767						4
3646768						5
3646769						6
3646770						8
3646771						10
3646772						12
3646773						(14)
3646774						16
3646775						20
1403044	M2	4	1,3	0,5	0,5	3
1403133						4
1403230						5
1403338						6
1403435						8
1403583						10
1403591						12
1403761	M2,5	5	1,5	0,6	0,6	4
1403869						5
1403958						6
1404040						8
1404059						10
1404156						12
1404164						16
1404172						20
1404180						25

M1,6; M2; M2,5: in accordance with ISO 1580

Article#	d ₁	d ₂	k	n	t min.	L
1577999	M3	6	1,8	0,8	0,7	4
1246267						5
1246275						6
1246283						8
1246291						10
1246305						12
1246313						16
1246321						20
1404199						25
1404202						30
1404229						40
1246348	M4	8	2,4	1,2	1	5
1246356						6
1246364						8
1246372						10
1246380						12
1246399						16
1246402						20
1246410						25
1246429						30
1404237						35
1404245						40
1404253						50
1246437	M5	10	3	1,2	1,2	6
1246445						8
1246453						10
1246461						12
1246488						16
1246496						20
1246518						25
1246526						30
1404644						35
1246534						40
1404695						50
1404741						60
1246542	M6	12	3,6	1,6	1,4	8
1246550						10
1246569						12
1246577						16
1246585						20
1246593						25

M1,6; M2; M2,5: in accordance with ISO 1580

Article#	d ₁	d ₂	k	n	t min.	L
1246607	M6	12	3,6	1,6	1,4	30
1404806						35
1246615						40