


# 15 Ampere, 125, 125/250 Volts Midget Twist-Lock Connector Bodies and Flanged Receptacles



**IP20**  
SUITABILITY



## Connector Bodies

| Description                                                                               | Cord Dia.                 | Catalog Numbers |                 |                 |
|-------------------------------------------------------------------------------------------|---------------------------|-----------------|-----------------|-----------------|
| Valise® connector body, black nylon, polarized.                                           | .220"-.385"<br>(5.6-9.8)  | <b>HBL7464V</b> | —               | —               |
| Valise® connector body, black nylon, insulation displacement terminals.                   | .300"-.430"<br>(7.6-10.9) | —               | <b>HBL7593V</b> | —               |
| Black nylon cover, phenolic body, screw terminals.                                        | .281"-.421"<br>(7.1-10.7) | —               | <b>HBL7593</b>  | —               |
| Angle connector body, black nylon cover, phenolic body, screw terminals.                  | .335"-.421"<br>(8.5-10.7) | —               | <b>HBL7571</b>  | —               |
| Valise® type, black nylon, with insulation displacement terminals, multiple drive screws. | .300"-.430"<br>(7.6-10.9) | —               | —               | <b>HBL7484V</b> |
| Black nylon body, phenolic base, multiple drive screws, cord grip.                        | .281"-.421"<br>(7.1-10.7) | —               | —               | <b>HBL7484</b>  |
| Same as above, except for angle cord grip.                                                | .335"-.421"<br>(8.5-10.7) | —               | —               | <b>HBL7433</b>  |

Accessories on page B-6.

## Flanged Receptacles


| Description                                                                       | Catalog Numbers |                 |                 |
|-----------------------------------------------------------------------------------|-----------------|-----------------|-----------------|
| Stainless steel flange, exposed terminals.                                        | <b>HBL7468</b>  | —               | —               |
| Exposed terminals, black nylon flange.                                            | —               | <b>HBL7596N</b> | —               |
| Exposed terminals, stainless steel flange.                                        | —               | <b>HBL7596</b>  | —               |
| Covered terminals, stainless steel flange, accepts cord .500" (12.7) in dia.      | —               | <b>HBL7598</b>  | —               |
| Exposed terminals, black nylon flange.                                            | —               | —               | <b>HBL7487N</b> |
| Exposed terminals, stainless steel flange.                                        | —               | —               | <b>HBL7487</b>  |
| Covered terminals, stainless steel flange, accepts cord .500" (12.7) in diameter. | —               | —               | <b>HBL7489</b>  |

Accessories on page B-6.

Notes: Male ML-2R devices have solid center ground pins.  
Male ML-3R devices have hollow center neutral sleeves.



**HBL7464V**




**HBL7593V**



**HBL7593**




**HBL7571**



**HBL7484V**




**HBL7484**




**HBL7596**



**HBL7598**



**HBL7596N**



**HBL7468**