

POWER SOURCES

WALLPLUG-IN/DESK-TOP

ADVANTAGES



- Keeps hazardous line voltage out of the product.
- Increases space for other components in the product.
- Improves aesthetic appearance and portability.
- Reduces size and weight of the product.
- Keeps power supply heat out of the product for increased life.
- Reduces product design time.


FEATURES

- Domestic Units
 - U.L. Listed
 - U.L.-1310 Class 2 Power Units
 - C.S.A. Certified
- European Units
 - CE Marked
- Output Cords 6 feet long
- Rated for Continuous Duty
- Available in A.C. and D.C. outputs

SPECIFICATIONS

- Input Voltages
 - Domestic (120V 60Hz), European (230V 50Hz)
 - Other voltages available as custom designs.
- Operating Temperature
 - -10° to +40° C
- Output Voltages Range from 2.5V to 24V
- Output Current Range from 50mA to 3400mA





CUSTOM DESIGN CAPABILITIES

- Various Case Colors
-- Pantone Number Required
- Varied length and style of output cord
- Custom nameplates and labels
- Primary input voltages for various countries
- 500 pieces minimum order and release for custom designs
- Optional output plug sizes, styles & polarities.

APPLICATIONS

- Computer Peripherals
- Portable Games
- Portable Consumer Products
- Telephone Answering Machines
- Laptop Computers
- Equipment Rechargers



EUROPEAN POWER SOURCES

European Desk-Top



European Wall Plug-In



Output power plugs:

Compatible for use with Switchcraft 722A or PC-722A


Input for All European Models is 230 Volts A.C., 50 Hz. with CEE 7/16 Europlug

SEC.	STANCOR PART NUMBER	Rated Output			Regulated/ Unregulated	Case Style	DIMENSIONS						Weight (lbs.)	Output Plug 2.1x5.5mm Inside Polarity	Compliance
		Volts	AC/DC	mA			Length (inches) (mm)		Width (inches) (mm)		Height (inches) (mm)				
A	STAF-0381F	6.0	DC	500	Unregulated	Wall Plug-in	2.5	63.5	2.0	50.8	1.6	39.7	0.55	Negative	CE
	STAF-0797F	6.0	DC	1000	Unregulated	Wall Plug-in	2.8	69.9	2.3	57.2	1.8	46.0	0.83	Negative	CE
	STAF-2100F	6.2	DC	300	Unregulated	Wall Plug-in	2.3	57.2	1.7	42.9	1.5	38.1	0.40	Negative	CE
	STAF-2223F	9.0	DC	200	Unregulated	Wall Plug-in	2.3	57.2	1.7	42.9	1.5	38.1	0.40	Negative	CE
B	STAF-3309F	9.0	DC	300	Unregulated	Wall Plug-in	2.5	63.5	2.0	50.8	1.6	39.7	0.49	Negative	CE
	STAF-1058F	9.0	DC	500	Unregulated	Wall Plug-in	2.5	63.5	2.0	50.8	1.6	39.7	0.55	Negative	CE
	STAF-0329F	9.0	DC	1000	Unregulated	Wall Plug-in	2.8	69.9	2.3	57.2	1.8	46.0	0.93	Negative	CE
	STAF-3382F	12.0	DC	300	Unregulated	Wall Plug-in	2.5	63.5	2.0	50.8	1.6	39.7	0.55	Negative	CE
C	STAF-1454FD	12.0	DC	1000	Unregulated	Desk-Top	3.4	85.7	2.6	65.1	2.2	55.6	1.60	Negative	CE
	STAF-1948FD	12.0	DC	1200	Unregulated	Desk-Top	3.4	85.7	2.6	65.1	2.2	55.6	1.60	Negative	CE
	STAF-0354F	14.5	DC	800	Unregulated	Wall Plug-in	2.8	69.9	2.3	57.2	1.8	46.0	1.00	Negative	CE
D	STAF-1972F	15.0	DC	1000	Unregulated	Desk-Top	3.4	85.7	2.6	65.1	2.2	55.6	1.60	Negative	CE
	STAF-2098F	24.0	AC	400	Unregulated	Wall Plug-in	2.8	69.9	2.2	55.6	1.8	46.0	0.85	-	CE



CE Mark

Wall Plug-In



Desk-Top

