

CONSOLETS



INDUSTRY STANDARDS

UL 508A Listed; Type 12, 13; File No. E61997
cUL Listed per CSA C22.2 No. 94; Type 12, 13; File No. E61997

NEMA/EEMAC Type 12, 13
CSA File Number 42186: Type 12
IEC 60529, IP65

APPLICATION

Consoles are ideal for mounting small control or instrumentation devices where the desirable access requires a 30- or 60-degree surface. These enclosures can be mounted on either of two sides for placement on desktops, pedestals or other flat surfaces.

SPECIFICATIONS

- 14 gauge steel
- Seams continuously welded and ground smooth; no holes or knockouts
- Captivated cover screws thread into sealed wells
- Bonding provision on cover
- Oil-resistant gasket and adhesive
- Control panel attached with continuous hinge along bottom edge

FINISH

ANSI 61 gray polyester powder paint inside and out over pretreated surfaces.

ACCESSORIES

See also Accessories.
Industrial Corrosion Inhibitors
Latch Kits for Type 4 and 12 Enclosures
Mounting Bracket Kits
Touch-Up Paint
Steel and Stainless Steel Window Kits






NOTES

See the Stainless Steel chapter for information on related stainless steel products.



BULLETIN: C5, P1

Standard Product Consoles

Catalog Number	AxBxC in./mm	E in./mm	H in./mm	J in./mm	K in./mm	L in./mm	N in./mm
C8C8	8.00 x 8.00 x 7.09 203 x 203 x 180	5.62 143	8.28 210	8.28 210	7.50 191	6.62 168	7.44 189
C8C12	8.00 x 12.00 x 7.09 203 x 305 x 180	5.62 143	8.28 210	12.28 312	11.50 292	6.62 168	7.44 189
C8C16	8.00 x 16.00 x 7.09 203 x 406 x 180	5.62 143	8.28 210	16.28 414	15.50 394	6.62 168	7.44 189
C8C20	8.00 x 20.00 x 7.09 203 x 508 x 180	5.62 143	8.28 210	20.28 515	19.50 495	6.62 168	7.44 189
C12C12	12.00 x 12.00 x 9.09 305 x 305 x 231	7.62 194	12.28 312	12.28 312	11.50 292	10.62 270	10.91 277
C12C16	12.00 x 16.00 x 9.09 305 x 406 x 231	7.62 194	12.28 312	16.28 414	15.50 394	10.62 270	10.91 277
C12C20	12.00 x 20.00 x 9.09 305 x 508 x 231	7.62 194	12.28 312	20.28 515	19.50 495	10.62 270	10.91 277
C12C24	12.00 x 24.00 x 9.09 305 x 610 x 231	7.62 194	12.28 312	24.28 617	23.50 597	10.62 270	10.91 277
C16C16	16.00 x 16.00 x 11.09 406 x 406 x 282	9.62 244	16.28 414	16.28 414	15.50 394	14.62 371	14.38 365
C16C20	16.00 x 20.00 x 11.09 406 x 508 x 282	9.62 244	16.28 414	20.28 515	19.50 495	14.62 371	14.38 365
C16C24	16.00 x 24.00 x 11.09 406 x 610 x 282	9.62 244	16.28 414	24.28 617	23.50 597	14.62 371	14.38 365
C16C30	16.00 x 30.00 x 11.09 406 x 762 x 282	9.62 244	16.28 414	30.28 769	29.50 749	14.62 371	14.38 365
C16C36	16.00 x 36.00 x 11.09 406 x 914 x 282	9.62 244	16.28 414	36.28 922	35.50 902	14.62 371	14.38 365
C20C20	20.00 x 20.00 x 13.09 508 x 508 x 332	11.62 295	20.28 515	20.28 515	18.62 473	18.62 473	17.84 453
C20C24	20.00 x 24.00 x 13.09 508 x 610 x 332	11.62 295	20.28 515	24.28 617	22.62 575	18.62 473	17.84 453
C20C30	20.00 x 30.00 x 13.09 508 x 762 x 332	11.62 295	20.28 515	30.28 769	28.62 727	18.62 473	17.84 453



SECTION Y-Y



C2760-C

Standard Product Pedestal Columns and Bases for Consolets

Catalog Number	AxBxC in./mm	Description
A44CCOL	35.00 x 4.00 x 4.00 889 x 102 x 102	Straight Pedestal Column
A66CCOL	35.00 x 6.00 x 6.00 889 x 152 x 152	Straight Pedestal Column
A18SBASE	18.00 x 18.00 457 x 457	Pedestal Base
A24SBASE	24.00 x 24.00 610 x 610	Pedestal Base