




- Collet Sockets available in Single or Dual Rows
- Cuttable to the number of pins desired to fit the application
- Side-to-side and end-to-end stackable



- **BODY MATERIAL:** Black UL 94V-0 Glass-filled 4/6 Nylon
- **PIN BODY:** Brass 360 1/2-hard per UNS C36000 ASTM B16/B16M-05
- **PIN BODY PLATING:** 10μ [0.25μ] min. Au per MIL-G-45204 –OR– 200μ [5.08μ] min. 93/7 Sn/Pb per ASTM B545 or 200μ [5.08μ] min. Sn per ASTM B545 Type I over 100μ [2.54μ] min. Ni per SAE AMS-QQ-N-290B
- **4-FINGER COLLET CONTACT:** BeCu per UNS C17200 ASTM B194-08
- **CONTACT PLATING:** 200μ [5.08μ] min. 93/7 Sn/Pb per ASTM B545 –OR– 200μ [5.08μ] min. Sn per ASTM B545 Type 1 or 10μ [0.25μ] Au per MIL-G-45204 over 50μ [1.27μ] min. [1.27μ] Ni per SAE AMS-QQ-N-290 Heavy 30μ [0.76μ]
- **CONTACT CURRENT RATING:** 3 amps
- **INSERTION FORCE:** 180g/pin, based on 0.018 [0.46] dia. test lead
- **WITHDRAWAL FORCE:** 90g/pin, based on 0.018 [0.46] dia. test lead
- **NORMAL FORCE:** 140g/pin, based on 0.018 [0.46] dia. test lead
- **OPERATING TEMPERATURE:** -67°F to 221°F [-55°C to 105°C] for Sn plating; -67°F to 257°F [-55°C to 125°C] for Au plating
- **INSERTION FORCE:** 180g/pin, based on 0.018 [0.46] dia. test lead
- **WITHDRAWAL FORCE:** 90g/pin, based on 0.018 [0.46] dia. test lead
- **NORMAL FORCE:** 140g/pin, based on 0.018 [0.46] dia. test lead
- **ACCEPTS LEADS:** 0.015-0.025 [0.38-0.64] dia.
- **LEAD LENGTHS:** from 0.100 [2.54] min.

XX X 518-1 XX XX

H = Heavy Au on Collet Shell
T = Sn Collet, Sn Shell
TL = Sn/Pb Collet & Shell
E = Extra Long Tail (0.183")


0 = Au Collet, RoHS Shell
OTL = Au Collet, Sn/Pb Shell
1 = Au Collet & Shell

Series

- No. of Rows
 - 0 = Single
 - 1 = Dual

- No. of Pins per Socket
 - 1 Row – 1 to 40 Pins
 - 2 Rows – 2 to 66 Pins

- **SUGGESTED PCB HOLE SIZE:** 0.030 ± 0.002 [0.76 ± 0.05] dia.



"A" = NO. OF PINS PER ROW x 0.100 [2.54]
 "B" = (NO. OF PINS PER ROW -1) x 0.100 [2.54]

**PRINTOUTS OF THIS DOCUMENT MAY BE OUT-OF-DATE AND SHOULD BE
CONSIDERED UNCONTROLLED**



2609 Bartram Road • Bristol, PA 19007-6810 USA
TEL 215-781-9956 • FAX 215-781-9845
WWW.ARIESELEC.COM • INFO@ARIESELEC.COM



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Aries Electronics:

[12-0518-10T](#) [40-0518-10](#) [30-1518-11](#) [19-0518-11H](#) [19-0518-10H](#) [19-0518-10T](#) [22-0518-11H](#) [22-1518-11H](#) [22-1518-10T](#) [22-1518-10H](#) [22-0518-10T](#) [22-0518-10H](#) [35-0518-11H](#) [35-0518-10H](#) [35-0518-10T](#) [11-0518-10H](#) [11-0518-10T](#) [11-0518-11H](#) [35-0518-11](#) [35-0518-10](#) [39-0518-11](#) [39-0518-10](#) [31-0518-10](#) [31-0518-11](#) [37-0518-10](#) [27-0518-11H](#) [37-0518-11](#) [27-0518-10H](#) [27-0518-10T](#) [33-0518-11](#) [33-0518-10](#) [38-0518-10](#) [38-1518-10](#) [38-1518-11](#) [38-0518-11](#) [30-1518-10](#) [30-0518-10](#) [30-0518-11](#) [34-0518-11](#) [34-1518-11](#) [34-1518-10](#) [34-0518-10](#) [32-1518-10](#) [32-0518-10](#) [32-0518-11](#) [32-1518-11](#) [03-0518-10H](#) [03-0518-10T](#) [03-0518-11H](#) [30-0518-11H](#) [30-1518-11H](#) [30-1518-10H](#) [30-1518-10T](#) [36-1518-11](#) [36-0518-11](#) [36-0518-10](#) [36-1518-10](#) [30-0518-10H](#) [30-0518-10T](#) [34-1518-11H](#) [34-0518-11H](#) [34-0518-10T](#) [34-0518-10H](#) [34-1518-10T](#) [34-1518-10H](#) [07-0518-11H](#) [07-0518-10T](#) [07-0518-10H](#) [10-0518-10H](#) [10-0518-10T](#) [10-1518-10H](#) [10-1518-10T](#) [10-0518-11H](#) [10-1518-11H](#) [26-0518-10T](#) [26-0518-10H](#) [26-1518-10H](#) [26-1518-10T](#) [26-0518-11H](#) [26-1518-11H](#) [39-0518-10T](#) [39-0518-10H](#) [39-0518-11H](#) [02-0518-11H](#) [02-1518-11H](#) [02-1518-10H](#) [02-1518-10T](#) [02-0518-10H](#) [02-0518-10T](#) [15-0518-11H](#) [15-0518-10T](#) [15-0518-10H](#) [23-0518-10T](#) [23-0518-10H](#) [23-0518-11H](#) [27-0518-11](#) [27-0518-10](#) [23-0518-10](#) [23-0518-11](#) [21-0518-10](#)