





DESCRIPTION: STD D-SUB SOCKET CONTACT, CRIMP
 MODEL NUMBER: 40-9864S, 40-9866S, 40-9866SK
 APPLICATION: FOR D-SUB
 CRIMP TOOL: N/A
 IMPEDANCE: N/A
 FREQUENCY RANGE: N/A
 MATERIAL: PHOSPHOR BRONZE GOLD PLATED
 WIRE RANGE: 24-28 AWG
 RoHS COMPLIANCE: YES
 TECHNICAL DETAIL: N/A



MODEL NUMBER	PACKAGE
40-9864S	25 PCS/BAG
40-9866S	100 PCS/BAG
40-9866SK	5K PCS/BAG



A-A SECTION B-B SECTION

 **EMERSON**
 Network Power
 Connectivity Solutions
 This PROPRIETARY Document
 is property of Emerson Network
 Power, Connectivity Solutions.
 It is a non-transferable and issued with
 a license to use. It is the property of
 Emerson Network Power, Connectivity
 Solutions and is not to be reproduced
 or disclosed without the express
 permission of Emerson Network Power,
 Connectivity Solutions.

3RD ANGLE PROJECTION

 RoHS2
 2011/65/EU

UNLESS OTHERWISE SPECIFIED
UNITS: METRIC

XX ±.51

XXX ±.127

ANGLES ±2°

INTERPRET DRAWING IN
ACCORDANCE WITH ASME
Y14.5-2009

AIM-Cambridge

Title:
D-SUB SOCKET CONTACT

Model No.
40-98(64S)(66S)(66SK)

Size DO NOT SCALE Date:
A DRAWING 12/10/2013 Sheet 1 of 1