

Mainstesters



4952 Mainstester
220-250V AC

DIN 57680-6, DIN VDE 0680-6:1972-04

Item Number			
440007	65mm	3mm	0.5mm

VDE approved mainstester. One piece moulded blade and handle with insulation for assured safety, high visibility permanently sealed resistance neon tube. Top quality chrome vanadium blade and nickel plated spring steel pocket clip.



4962 Mainstester
220-250V AC

DIN 57680-6, DIN VDE 0680-6:1972-04

Item Number			
440012	100mm	4mm	0.6mm

VDE approved mainstester. One piece moulded blade and handle with insulation for assured safety, high visibility permanently sealed resistance neon tube. Top quality chrome vanadium blade.

Mainstesters should not be used as screwdrivers.

Contact customer services on:

UK:
Tel: 01758 704 704 Fax: 01758 704 705
Email: sales@cki.uk.com

Republic of Ireland:
Tel: 1-800818 660 Fax: 1-800818 659
Email: dublin-sales@cki.uk.com

Rest of World:
Tel: +49 (0) 202 89030 Fax: +49 (0) 202 890322
Email: info@cki.de.com



4963 Mainstester heavy duty
100-250V AC

Item Number			
440013	120mm	4mm	0.6mm

Item Number		
540014	box of 440013	20

One piece moulded blade and handle with insulation for assured safety, high visibility permanently sealed resistance neon tube. Top quality chrome vanadium blade long pattern. Heavy duty.



4956/7 Mainstester
125-250V AC

DIN 57680-6, DIN VDE 0680-6:1972-04

Item Number		
440008	150mm	3mm
440009	190mm	3.5mm

The blade is nickel plated. Strong black plastic body with an integral pocket clip, hanging hole and anti-slip guard. The bulb is a clear easy to see bight neon.

These mainstesters meet the safety standard for single pole mainstesters where the bulb section is tamperproof. If opened the assembly cannot be refitted, so it renders the tester useless. VDE approved mainstesters for the best in single pole mainstester reliability and safety.

Toolkits

We use our in-depth knowledge of the requirements of end-users to put together kits of the most useful tools.



9500 Electrician's tool pouch kit

Item Number	
595002	Electrician's tool pouch kit

contains

Item Number		
416001	Tool Wallet	–
440009	Mainstester VDE	125 – 250V AC
T3442 16	ST Tape measure	5m / 16'
341012	SensoPlus® VDE screwdriver	PZ 2
341019	SensoPlus® VDE screwdriver	3 x 100
341021	SensoPlus® VDE screwdriver	4 x 100
431008	RedLine™ VDE combicutter3	160mm
492001	Electricians scissors	140mm
T3482	Pocket level	8¼"
495028	Re-threading tool	M3.5 x 6



36070 Pliers and Screwdriver kit
PZ

Item Number	
331001	Pliers and Screwdriver kit UK PZ

contains

Item Number		
431004	RedLine™ VDE combicutter1	165mm
431012	RedLine™ VDE stripping pliers	200mm
431013	RedLine™ VDE snipe pliers	170mm
341018	SensoPlus® VDE screwdriver	2.5 x 75mm
341019	SensoPlus® VDE screwdriver	3.0 x 100mm
341022	SensoPlus® VDE screwdriver	5.5 x 125mm
341011	SensoPlus® VDE screwdriver PZD	1 x 80
341012	SensoPlus® VDE screwdriver PZD	2 x 100
440077	Mainstester	65mm
416001	Tool wallet	–

36070 Pliers and Screwdriver kit
PH

Item Number	
331002	Pliers and Screwdriver kit UK PH

contains

Item Number		
431004	RedLine™ VDE combicutter1	165mm
431012	RedLine™ VDE stripping pliers	200mm
431013	RedLine™ VDE snipe pliers	170mm
341018	SensoPlus® VDE screwdriver	2.5 x 75mm
341019	SensoPlus® VDE screwdriver	3.0 x 100mm
341022	SensoPlus® VDE screwdriver	5.5 x 125mm
341003	SensoPlus® VDE screwdriver PH	1 x 80
341002	SensoPlus® VDE screwdriver PH	2 x 100
440077	Mainstester	65mm
416001	Tool wallet	–

36070 Pliers and Screwdriver kit
EXP PZ

Item Number		i
331003	Pliers and Screwdriver kit EXP PZ	

contains

Item Number		i	
431017	RedLine™ VDE side cutters	160mm	
431012	RedLine™ VDE stripping pliers	200mm	
431013	RedLine™ VDE snipe pliers	170mm	
341018	SensoPlus® VDE screwdriver	2.5 x 75mm	
341019	SensoPlus® VDE screwdriver	3.0 x 100mm	
341022	SensoPlus® VDE screwdriver	5.5 x 125mm	
341011	SensoPlus® VDE screwdriver PZD	1 x 80	
341012	SensoPlus® VDE screwdriver PZD	2 x 100	
440077	Mainstester	65mm	
416001	Tool wallet	–	

36070 Pliers and Screwdriver kit
EXP PH

Item Number		i
331004	Pliers and Screwdriver kit EXP PH	

contains

Item Number		i	
431017	RedLine™ VDE side cutters	160mm	
431012	RedLine™ VDE stripping pliers	200mm	
431013	RedLine™ VDE snipe pliers	170mm	
341018	SensoPlus® VDE screwdriver	2.5 x 75mm	
341019	SensoPlus® VDE screwdriver	3.0 x 100mm	
341022	SensoPlus® VDE screwdriver	5.5 x 125mm	
341003	SensoPlus® VDE screwdriver PH	1 x 80	
341004	SensoPlus® VDE screwdriver PH	2 x 100	
440077	Mainstester	65mm	
416001	Tool wallet	–	

For our comprehensive range of electrician’s pliers & cutters, please see pages 14-16.



9500 Electrician's premium kit

Item Number		i
595003	Electrician’s premium kit	

contains

Item Number		i	
T1630	Technician's tool case	–	
431003	RedLine™ VDE Combination plier	185mm	
431013	RedLine™ VDE Snipe nose plier	175mm	
431008	RedLine™ VDE Combicutter3	–	
341018	SensoPlus® VDE screwdriver	2.5 x 75	
341021	SensoPlus® VDE screwdriver	4 x 100	
341003	SensoPlus® VDE screwdriver	PH 1	
341004	SensoPlus® VDE screwdriver	PH 2	
341011	SensoPlus® VDE screwdriver	PZ 1	
341012	SensoPlus® VDE screwdriver	PZ 2	
T0834	Junior Hacksaw	–	
T3442 25	ST Tape measure	7.5m / 25’	
484001	Electricians knife	–	
495001	Automatic Wire Stripper	–	
T3482	Level-Pocket	210mm / 8 ¼’	
440009	Mainstester VDE	125-250V AC	
T4229 16	Claw Hammer	16oz	
495028	Re-Threading tool	M3.5 x 6	
340002	Modulo screwdriver	Size 2	



9500 Electrician's premium kit euro

Item Number		i
T1630 FKIT	Electrician’s premium kit euro	

contains

Item Number		i	
T1630	Technician's tool case	–	
T0836A	Mini Hacksaw	–	
T10280	Cable knife	–	
T20040	Auto Stripper no.54	–	
340001	Modulo screwdriver	Size 1	
340002	Modulo screwdriver	Size 2	
341011	SensoPlus® VDE screwdriver	PZ 1	
341018	SensoPlus® VDE screwdriver	2.3 x 75	
341021	SensoPlus® VDE screwdriver	4 x 100	
341003	SensoPlus® VDE screwdriver	PH 1	
341004	SensoPlus® VDE screwdriver	PH 2	
484001	Electricians knife	–	
431003	RedLine™ VDE Combination plier	175mm	
431017	RedLine™ VDE Side cutter	160mm	
431013	RedLine™ VDE Snipe nose plier	175mm	
T3442M 8	ST Tape measure	8M	
440007	VDE Mainstester	220-250V AC	
495002	Universal switch key wrench	–	
T0831	Plasterboard saw	–	



9500 Electrician's starter kit

Item Number		i
595001	Electrician’s starter kit	

contains

Item Number		i	
T1715	Electrician’s toolbelt set	–	
T3442 16	ST Tape measure	5m / 16’	
440009	Mainstester VDE	125 – 250V AC	
T0834	Junior hacksaw	–	
T3482	Pocket level	210mm	
484001	Electricians knife	–	
431008	RedLine™ VDE combicutter3	–	
431013	RedLine™ VDE snipe nose plier	170mm	
431003	RedLine™ VDE combination plier	185mm	
341012	SensoPlus® VDE screwdriver PZ	2	
341018	SensoPlus® VDE screwdriver	2.5 x 75	
341022	SensoPlus® VDE screwdriver	5.5 x 125	
341023	SensoPlus® VDE screwdriver	6.5 x 150	
340002	Modulo screwdriver	Size 2	

For our comprehensive range of electrician's screwdrivers, please see pages 45-47.



Hexagon Keys



4411 Hex Keys

ISO 2936

Item Number				
T4411 007	0.7mm	32mm	6mm	0.4g
T4411 009	0.9mm	32mm	10mm	0.5g
T4411 01	1.0mm	32mm	10mm	0.5g
T4411 012	1.2mm	38mm	10mm	0.6g
T4411 0127	1.27mm	40mm	12mm	0.6g
T4411 015	1.5mm	45mm	14mm	0.9g
T4411 02	2.0mm	50mm	16mm	1.5g
T4411 025	2.5mm	56mm	18mm	3.0g
T4411 03	3.0mm	63mm	20mm	5.0g
T4411 035	3.5mm	67mm	23mm	7.5g
T4411 04	4.0mm	71mm	25mm	9.5g
T4411 045	4.5mm	75mm	26mm	11.5g
T4411 05	5.0mm	80mm	28mm	18.0g
T4411 055	5.5mm	85mm	30mm	19.0g
T4411 06	6.0mm	90mm	32mm	29.0g
T4411 07	7.0mm	95mm	34mm	42.0g
T4411 08	8.0mm	100mm	36mm	58.0g
T4411 09	9.0mm	105mm	38mm	78.0g
T4411 10	10.0mm	112mm	40mm	102.0g
T4411 11	11.0mm	118mm	43mm	130.0g
T4411 12	12.0mm	125mm	45mm	164.0g
T4411 13	13.0mm	133mm	50mm	207.0g
T4411 14	14.0mm	140mm	56mm	258.0g
T4411 15	15.0mm	147mm	58mm	310.0g
T4411 16	16.0mm	154mm	60mm	369.0g
T4411 17	17.0mm	160mm	63mm	425.0g
T4411 18	18.0mm	170mm	65mm	507.0g
T4411 19	19.0mm	180mm	70mm	606.0g
T4411 20	20.0mm	187mm	73mm	703.0g
T4411 22	22.0mm	200mm	80mm	923.0g

Standard length metric.

The chrome vanadium steel is specially hardened so the key doesn't twist or 'round off'



4404 Hex Key folding set

Item Number		
T4404A	Metric 2.5, 3, 4, 5, 6, 7, 8mm	7pc

Clip holder is made from heavy gauge nickel-plated steel.



4405 Hex Key folding set

Item Number		
T4405A	Imperial AF 3/32, 1/8, 5/32, 3/16, 7/16, 1/2, 5/16"	7pc

Clip holder is made from heavy gauge nickel-plated steel.



4407 Hex Key folding set

Item Number		
T4407	torx tamperproof T06, T07, T08, T09, T10, T15, T20, T25	8pc


Torx tamperproof keys in a clip holder



4414 Hex Key ring set

Item Number		
T4414	Imperial AF 1/16, 5/64, 3/32, 1/8, 5/32, 3/16, 7/32, 1/4"	8pc


High quality hex keys on handy ring.



4415 Hex Key ring set

Item Number		
T4415	Imperial AF 1/16, 5/64, 3/32, 1/8, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8"	10pc


High quality hex keys on handy ring.



4416 Hex Key ring set

Item Number		
T4416	Metric 1.5, 2, 2.5, 3, 4, 5, 6, 7, 8, 10mm	10pc

High quality hex keys on handy ring.



4417 Hex Key ring set

Item Number		
T4417	Metric 1.5, 2, 2.5, 3, 4, 5, 6, 7mm	8pc

High quality hex keys on handy ring.

Ball-ended keys can be used at an angle of up to 25°, which is particularly useful when there is restricted access.



4443 Hex Key clip set ball ended

Item Number		
T4443M	Metric 1.5, 2, 2.5, 3, 4, 5, 6, 7, 8, 10mm	10pc

Set supplied in a convenient clip and store bracket.



4444 Hex Key clip set ball ended

Item Number		
T4444I	Imperial AF 5/64, 3/32, 1/8, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8"	10pc

Set supplied in a convenient clip and store bracket.

Forged from Chrome Vanadium steel, all products in the C.K range have a non-slip satin chrome finish giving maximum resistance to rust and peeling.



C.K socketry products use the C.K 'sure drive' system, which means the torque is applied to the flat of the nut rather than the corners, so 'rounding off' is avoided.



4655 Socket Set
Metric – 1/4" Drive

Item Number	i	
T4655	39pc	1/4"

Set contains:
Sockets: 4, 4.5, 5, 5.5, 6, 7, 8, 9, 10, 11, 12, 13, 14mm
Socket Bits: Hexagon 3, 4, 5, 6mm
Tamper proof T 8, 10, 15, 20, 25, 27, 30, 40, PZD 1, 2, 3, PH 1, 2, 3, Slotted 4, 5.5, 7mm
Accessories: 50mm extension, 50mm extension/driver, Universal joint, Adaptor, 45 tooth quick release ratchet.



4656 Socket Set
Metric – 3/8" Drive

Item Number	i	
T4656	23pc	3/8"

Set contains:
Sockets: 6, 7, 8, 9, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19, 20, 21, 22, 24mm
Slotted 4, 5.5, 7mm
Accessories: 75mm extension, 150mm extension/driver, T-bar / 1/2" Adaptor, Universal joint, 45 tooth quick release ratchet.



4657 Socket Set
Metric – 1/2" Drive

Item Number	i	
T4657	22pc	1/2"

Set contains:
Sockets: 10, 11, 12, 13, 14, 15, 16, 17, 18, 19, 22, 24, 27, 30, 32mm – Extra sockets 16, 21mm
125mm & 250mm extension, T-bar / 3/8" Adaptor, Universal joint, 45 tooth quick release ratchet.



4690M Bi Hex Sockets
1/2" Drive

Item Number	
T4690M 10	10mm
T4690M 11	11mm
T4690M 12	12mm
T4690M 13	13mm
T4690M 14	14mm
T4690M 15	15mm
T4690M 16	16mm
T4690M 17	17mm
T4690M 18	18mm
T4690M 19	19mm
T4690M 20	20mm
T4690M 21	21mm
T4690M 22	22mm
T4690M 23	23mm
T4690M 24	24mm
T4690M 27	27mm
T4690M 30	30mm
T4690M 32	32mm

Hexagon pattern.



4692 Flexible Handle
1/2" Drive

Item Number	
T4692	430mm 17"



4693 Long Extension
1/2" Drive

Item Number	
T4693	250mm 10"



4694 Short Extension
1/2" Drive

Item Number	
T4694	125mm 5"



4695 T Handle
1/2" Drive

Item Number	
T4695	250mm 10"



4696 Universal Joint
1/2" Drive

Item Number
T4696



4463 Torque wrench

DIN ISO 3122

Item Number	i	
T4463	42-210Nm / 30-154lb-ft	600mm 18"

1/2" square drive with reversible ratchet head, calibrated in Nm and Mkg, settings etched on barrel. Micrometer type sleeve ensures accurate setting of torque. Each wrench is individually calibrated and supplied with a Certificate of Calibration. Marked range 42-210Nm/ 30-154lb-ft. Contained in strong storage case with 120mm extension and 3/8" adaptor.



4691 Ratchet Handle

1/2" Drive

Item Number	i	
T4691	1/2" ratchet drive	45 tooth

45 teeth. 8° working arc. A reversible ratchet handle with a dual component 'non-slip' grip and push button socket release.



4603 Ratchet Handle

1/2" Drive

Item Number	i	i
T4603	1/2" ratchet drive	24 tooth
T4603 1	repair kit	

24 teeth. 15° working arc. A reversible ratchet handle with push button socket release.



4645 1/2" Drive accessory bar

Item Number	i
T4645S	stock for accessory bar
T4645L	empty accessory bar
T4645H	header for empty accessory bar

contains

Item Number	i
T4691	1/2" drive ratchet
T4692	1/2" drive flexible handle – 430mm
T4693	1/2" drive extension – 250mm
T4694	1/2" drive extension – 125mm
T4695	1/2" drive sliding T handle
T4696	1/2" drive universal joint
T4697	1/2" drive 3/8" adaptor

A ratchet handle contains a one-way mechanism which allows the socket to be turned without removing it from the nut or bolt, simply by cycling the handle backwards and forwards. They contain teeth, and are available with different quantities of teeth. The larger the number of teeth, less the handle needs to be turned (working arc) to pick up the next tooth, which is very useful for working in restricted space. However the teeth are thinner, and therefore weaker, so there is a trade off between strength and working arc. Users should pick the tool most appropriate for their requirements.

Spanner & Wrenches



4343M Combination spanner
Metric

DIN 3113

Item Number		
T4343M 06	6mm	100mm
T4343M 07	7mm	110mm
T4343M 08	8mm	120mm
T4343M 09	9mm	130mm
T4343M 10	10mm	140mm
T4343M 11	11mm	150mm
T4343M 12	12mm	160mm
T4343M 13	13mm	170mm
T4343M 14	14mm	180mm
T4343M 15	15mm	190mm
T4343M 16	16mm	200mm
T4343M 17	17mm	210mm
T4343M 18	18mm	220mm
T4343M 19	19mm	230mm
T4343M 20	20mm	240mm
T4343M 21	21mm	250mm
T4343M 22	22mm	260mm
T4343M 24	24mm	280mm
T4343M 27	27mm	310mm
T4343M 30	30mm	340mm
T4343M 32	32mm	360mm

With a 12° offset bi-hexagon ring.



4343M Combination spanner
set of 10

Item Number	
T4343M/10ST	8, 9, 10, 11, 12, 13, 14, 15, 17 & 19mm

Set of ten metric combination spanners with wall mounting rack. Display packed. Contains one each of sizes listed above.



4343M Combination spanner
set of 12

Item Number	
T4343M/12ST	8, 9, 10, 11, 12, 13, 14, 15, 17, 19, 21 & 22mm

Set of 12 metric combination spanners in wall mounting/carry rack. Containing one of each sizes listed above.



4343M/21 Spanner display

Item Number	i
T4343M/21S	stock for spanner display
T4343M/21L	empty stand
T4343M/21H	header for empty stand

contains

Item Number	i
T4343M	5 x 6-24mm, 3 x 27-32mm



4345 Speed spanner set of 6

Item Number	
T4345M/6ST	10, 12, 13, 14, 15 & 17mm

These spanners feature an innovative jaw design which allows the spanners to be used with a 'ratchet' action ensuring fast work. The 'ratchet' action doesn't need excessive spanner movement making them very convenient in tight places. The colour coding aids in the quick selection of the correct size.



4381 Open Spanner Double ended

Item Number		
T4381	24 x 32mm	255mm

Hot drop forged carbon steel, hardened and tempered for strength and durability.



4382 Open Spanner Single ended

Item Number		
T4382	39mm	300mm

Hot drop forged carbon steel, hardened and tempered for strength and durability.



4347 Immersion heater spanner

Item Number	
T4347	85mm

For the installation and removal of electric immersion heaters fitted in domestic hot water cylinders. Soft grip handle for comfort and maximum torque, whilst the one piece manufacture enables full transmission of power to the spanner.



4365 Adjustable wrench Sure Drive

Item Number	
T4365 150	150mm 6"
T4365 200	200mm 8"
T4365 250	250mm 10"
T4365 300	300mm 12"

This 'sure drive' adjustable wrench includes both metric and inch graduations, an 18% wider jaw opening than standard patterns, a lightweight design and narrow jaw. All the features combine to ensure benefits in use over standard patterns.

The 'sure drive' jaw profile grips bolt heads and nuts at the flanks rather than the corners, so 'rounding off' is avoided.



4366 Adjustable wrench Wide Jaw

Item Number		
T4366 150	150mm 6"	0.24
T4366 200	200mm 8"	0.29
T4366 250	250mm 10"	0.33
T4366 300	300mm 12"	0.38
T4366 375	375mm 15"	0.51
T4366 450	450mm 18"	0.60

Regular Jaw / Wide Jaw comparison

150mm 6"	0 - 19mm 3/4"	0 - 24mm 5/16"	+5mm	+26%
200mm 8"	0 - 24mm 15/16"	0 - 29mm 1 1/8"	+5mm	+21%
250mm 10"	0 - 29mm 1 1/8"	0 - 33mm 1 5/32"	+4mm	+14%
300mm 12"	0 - 34mm 1 5/16"	0 - 38mm 1 1/2"	+4mm	+12%
350mm 15"	43mm 1 11/16"	0 - 51mm 2"	+8mm	+19%
450mm 18"	53mm 2 1/12"	0 - 60mm 2 3/8"	+7mm	+13%

Designed with a wider jaw than standard wrenches so a smaller size can be used, allowing access into tighter spaces.



4311 Basin wrench

Item Number	
T4311	basin wrench

The square telescopic pipe is adjustable in length to four positions between 275 and 460mm. The tool has a sliding T handle and a toothed, spring loaded self-adjusting, 180° swivelling forged steel jaws.



3735 Stillson wrench

Item Number	
T3735 300	300mm 12"
T3735 350	350mm 14"
T3735 450	450mm 18"
T3735 600	600mm 24"

Professional quality drop forged hardened and tempered wrench. Patented head design which allows greater torque before deformation. Serrated hardened jaws give secure grip and long life. Heat treated textured, durable paint finish gives greater control. Conforms to torque requirements of BS 3594. With hanging hole in handle.



4451 Switch Key universal

Item Number	
495002	

This multi purpose key designed for many uses, these include locking systems of gas, electric and water cupboards in industry and/or technical equipment in buildings such as air conditioning, stop valves, mains consoles etc.



4453 Universal key

Item Number	
495015	



4451-1 Universal switch key

Item Number	i
T4451-1	○●○○○▲◇⊕
M4451	switch key product highlighter

Compact pen-style key, designed to be stored with ease and fit conveniently in the pocket.

Measuring & Marking



3442 ST tape
Accurate to 73/362/EEC Class II

Item Number		i
T3442 10	3m 10ft	metric/imperial
T3442 16	5m 16ft	metric/imperial
T3442 25	7.5m 25ft	metric/imperial
T3442M 3	3m –	metric
T3442M 5	5m –	metric
T3442M 8	8m –	metric

The st tape range is constructed from tough, soft touch ABS plastic bodies with full lock and pause button facilities plus a belt clip. The blades are abrasion resistant nylon coated for wear and corrosion resistance and feature continuous metric/imperial graduations, 16” joist centre markings, and true zero hooks. Recoil dampers are provided on larger models for blade protection.



6100 Tape 5
Accurate to 73/362/EEC Class II

Item Number		i
461003	5m 16ft	tape measure
461015	5m 16ft	clipstrip x6
561003	5m 16ft	counterbox x12
461005	7.5m 25ft	tape measure
461016	7.5m 25ft	clipstrip x6
561005	7.5m 25ft	counterbox x12

The autobrake system automatically holds the tape out - you have to press the button to retract it. The magnetic rubber grip hook attaches to steel and curved objects and slippery edges. The big blade stand out is extremely useful when measuring over obstacles and the tough ABS/rubber body protects the tape from damage.



3561 Measuring tape
fibre

Item Number		
T3561 100	30m 100ft	13mm 1/2"

Manufactured in a vinyl coated glass fibre, accurate to Class III and comes in a strong ABS plastic case.




3563 Measuring tape
steel nylon coated

Item Number		
T3563 100	30m 100ft	13mm 1/2"


This nylon coated steel tape has Class II accuracy, comes in a protective steel case and has an excellent abrasion resistance for a long life.

The latest European legislation relating to accuracy of measuring instruments is directive 2004/22/EC.

This legislation gives ranges of tolerances on the graduations of equipment, that must be adhered to if conformity is being claimed. There are 3 classes of accuracy that are generally applied to different equipment depending on use. Class I is the most accurate, and might be used on tools such as engineer's rules, where high accuracy is required and can be achieved. Class II is the next level, and might be used on equipment such as tape measures.



Class III is the least demanding level and might be used on equipment which can be effected by temperature and stretching. Items such as top quality surveyor's tapes would achieve Class III accuracy.



Tools such as tapes that do not carry a class marking may be less accurate, and so could cause problems where high tolerances are required.



3565 Measuring tape
surveyors

Item Number		
T3565 100	30m 100ft	13mm 1/2"
T3565 165	50m 165ft	13mm 1/2"
T3565 330	100m 300ft	13mm 1/2"

Manufactured to class III accuracy, this tape has high glass fibre content to minimise stretching. Metric on one side and imperial on the other. Firm anchoring blade hook. Comfortable, large padded handle.



3510 Wooden rule
metric/imperial

Item Number	
T3510	1m 3ft

Professional quality, four fold with heavy brass hinge and tips. “Blindman’s” markings on both sides. Graduation - 5mm top edge, 1mm lower edge on one side; on reverse. 1/8”.



3530 Steel rule
metric/imperial

Item Number		
T3530 06	150mm 6"	18mm
T3530 12	300mm 12"	25mm

Stainless steel rule with hanging hole. Graduated on one side. Graduation - 0.5mm, 1mm upper edge, 1/64", 1/32", 1/16" lower edge.



3531 Straight edge/rule

Item Number	
T3531 100	1000mm 40"

For cutting, measuring and marking. Manufactured from anodised aluminium with strong plastic handle and hanging hole. Metric Graduations.



3492 Plumb bob

Item Number	
T3492 11	300g 11oz

The conical, fully polished bob comes complete with a screwed brass cord fitting.



3517 Chalk line cotton

Item Number	
T3517	18m 60ft

Single 18m/60ft hank.



3519 Chalk line braided nylon

Item Number	
T3519	18m 60ft

Single 18m/60ft hank.



3490 Line pins

Item Number	
T3531 100	170mm 6½"

Forged, nickel plated line pins, suitable for use in wet and dry mortar. Sold as a pair.



3520 Reel & Chalk

Item Number	
T3520A	30m 100ft

Black lacquered die cast metal case with fold-away winding handle. 30m self chalking line with end support hook, 45° and 90° angle markings. Supplied with 60g chalk.



3522 Reel & Chalk

Item Number	
T3522	30m 100ft

Lightweight thermoplastic case with fold-away winding handle. 30m self chalking line with end support hook. Supplied with 60g chalk.



3521 Chalk powder

Item Number		
T3521B 100	blue	100g 4oz
T3521R 100	red	100g 4oz

Container with 100g/4oz of chalk powder. Choice of two colours.



3540 Joiners square rosewood

Item Number		
T3540 09	225mm 9"	278g
T3540 12	300mm 12"	349g

Hardened and tempered blue steel blade held securely with 3 brass rivets. With brass inside face.



3541 Sliding bevel rosewood

Item Number	
T3541 9	225mm 9"


Hardened and tempered blue steel blade with quick locking lever.



3543 Marking & Mortice gauge rosewood

Item Number	
T3543	190mm 7½"


Screw adjustment for accurate setting of mortice and tenon joints.



3533 Joiners square beech

Item Number	
T3533 09	225mm 9"

Hardened and tempered blue steel blade held securely with 3 brass rivets. With brass inside face.



3537 Sliding bevel beech

Item Number	
T3537 09	230mm 9"

Blue steel spring blade.



3542 Marking gauge beech

Item Number			
T3542A	240mm	9 1/2"	

One hardened marking pin and plastic thumbscrew.



1125 Carpenter's pencil

Item Number	
T1125 24	carpenter's pencil


Wooden carpenters pencil 9 1/2" in length.



1531 Scriber

Item Number	
T1531	tile scriber

Tungsten carbide tipped, suitable for tiles, metal and glass. Pocket clip.



3579 Combination square

Item Number			
T3579	300mm	12"	1mm & 1/16" 1mm & 1/32"

Black metal stock, centre and protractor heads, all with brass setting screw. Stock incorporates scriber and level. Protractor and rule clearly defined in black. Metric and imperial graduation.



3581 Combination square

Item Number			
T3581	300mm	12"	1mm & 1/16" 1mm & 1/32"

Heavy duty stock, centre and protractor heads, all with brass setting screw. Stock incorporates scriber and level. Protractor and rule clearly defined in black. Metric and imperial graduation.



3582 Combination square

Item Number			
T3582	300mm	12"	1mm & 1/16" 1mm & 1/32"

Black metal stock with brass adjustment screw, scriber and level. Metric and imperial graduation clearly defined on polished steel blade.



3525 Feeler gauge

Item Number			
T3525 413	100mm	4"	imperial
T3525M 413	100mm	4"	metric

The 100mm (4") tapered blades have electrically etched numbers. The blades fold into a metal case. T3525 413 Contents: 13 blades 2, 3, 4, 5, 6, 8, 10, 12, 15, 20, 25, 30 and 35/1000". T3525M 413 Contents: 13 blades 0.05, 0.1, 0.15, 0.2, 0.25, 0.3, 0.4, 0.5, 0.6, 0.7, 0.8, 0.9 and 1mm.



3451 Vernier caliper

Item Number			
T3451	125mm	5"	Graduation 0.1mm / 1/128"

Designed with a roller adjustment and nickel plated. Can be used for internal, external and depth measurements.



6202 Pocket balance

Item Number		
T6202 025	12.5kg	25lb
T6202 032	15kg	32lb
T6202 044	20kg	44lb
T6202 050	23kg	50lb
T6202 066	30kg	66lb
T6202 088	40kg	88lb
T6202 112	50kg	112lb

Calibrated in 1lb / 1/2kg divisions. Brassed scale, black lacquered body, tinned hook and ring.

Levels



3482 Pocket level

Item Number		
T3482	210mm	8 1/4"

Multi-purpose pocket level with detachable mini level. The pocket level has 1 horizontal vial, 1 vertical vial and a magnetic base. The removable mini level also has a magnetic base and can be used as line level.



3494 Aluminium level

Item Number			
T3494 18	2 vial with rule	400mm	18"
T3494 24	2 vial with rule	600mm	24"
T3494 32	3 vial with rule	800mm	32"
T3494 40	3 vial with rule	1000mm	40"
T3494 48	3 vial	1200mm	48"
T3494 70	3 vial	1800mm	70"

Item Number	
M3494	spirt level header card



Aluminium box section level accurate to ± 0.5mm per metre. It has shock-proof unbreakable vials, and the luminous horizontal vial allows measuring in dim environments.

A straightforward range of levels for tradesmen.

When we set out to produce a new first fix saw the brief was simple. Produce a high quality multi-purpose saw with a cutting ability that would be second to none when measured against the leading saws currently on the market.

We were not interested in being nearly as good, or even as good as. We were determined to set new standards in cutting ability both in initial speed of cut and also retained sharpness.

Tests conducted to cut 100 blocks



First fix saw tested against UK's market leading saws in independent CATRA tests.

The result was the new C.K Sabretooth first fix saw.

Based on a triple ground hardpoint cutting edge with a rigid 1mm blade we knew that this was indeed a superb saw. And when the results of the independant tests by CATRA were revealed we knew we had achieved our objective. Take a look at the test results and you'll see why. C.K Sabretooth came out top on initial strokes and even after cutting 100 test blocks was far in the lead.



8100 Sabretooth saw

Item Number		i	×
481001	22'	7tpi / 8ppi	1
581001		box of saws	10

Item Number		i	×
481002	22'	11tpi / 12ppi	1
581002		box of saws	10

Item Number		i
M8100	Sabretooth saw dumpbin	
M8101	Sabretooth saw pallet sleeve	
M8102	Sabretooth saw poster	

Triple edge, precision ground, hard point, rigid 1mm blade, easy start, fast cut on push and pull. Available in first and second fix.



814 Quick Change hacksaw

Item Number		tpi
T0814	300mm 12'	24

Heavy duty, quality hacksaw with comfortable rubber grips. Easy blade change using the quick release slide catch. Blade tension adjustment. 45° & 90° blade positions. Spare blade storage in sturdy back frame.



903 Hacksaw

Item Number		tpi
T0903 12	300mm 12'	24

Robust heavy duty hacksaw with aluminium handle and sturdy box section steel frame.



905 Hacksaw

Item Number		tpi
T0905	300mm 12'	24

Robust heavy duty hacksaw with aluminium handle and sturdy box section steel frame. Blade tension lever integrated into handle for quick change of blades. Blade adjustable in 45° position.



931/2/3/4 HSS Bi Metal hacksaw blades

Item Number		tpi	×
T0931R 12	300mm 12'	24	3
T0932R 12	300mm 12'	18	1
T0933R 12	300mm 12'	24	1
T0934R 12	300mm 12'	32	1

1/2" wide, blue lacquered blade.

C.K hacksaw blades are constructed with 2 different types of metal. The back is made from a tough, flexible alloy, while the teeth are made from a hard steel. This means the blade is flexible, and unlike 'all-hard' blades which are brittle, is far less likely to break under stress.



930L Hacksaw blade display

Item Number	i
T0930L	empty hacksaw display stand. No header
T0930H	header for T0930L. Stock pack not available

Capable of holding approximately 450 blades. Header gives information in regard to choosing the correct blade for the job in hand. For the HSS Bi-metal blades 932, 933, 934. Dimensions for stand are 390 x 215 x 115mm.



836 Mini hacksaw

Item Number	
T0836A	150mm 6'

Strong rigid aluminium frame with comfortable handle. Supplied with top quality metal cutting blade. Adjustable to 6 cutting positions. Fast easy blade fitting with screw tensioning.



837 Mini hacksaw and mitre box

Item Number	
T0837	300mm 12'

Mini hacksaw T0836A packed together with a lightweight plastic mitrebox with 3 cutting angles and extended lip for easy placement on work surface.



834 Junior hacksaw

Item Number		tpi
T0834	150mm 6'	32

Red epoxy coated steel frame 58mm/2 1/4" deep. The pins of blade are fixed in frame and do not therefore protrude to injure the hand. Comes complete with one top quality 150mm/6" 32tpi blade fitted plus one spare.



835 Junior hacksaw blades

Item Number		tpi	×
T0835	150mm 6'	32	10

Top quality general purpose metal cutting blades with pinned end to fit standard junior hacksaw frames. Packed in quantities of 10.



831 Plasterboard saw

Item Number	
T0831	150mm 6'

Also known as a dry wall saw, designed for cutting holes in plasterboard for sockets and conduits.

Knives



9039 Pocket knife locking

Item Number	
484001	95mm 3 3/4"

The polished blade features a wire stripping notch and locking function for safety.

Our general purpose pocket knives have fully hardened, finely ground blades ensuring clean cut. The brass rivets give extra rust resistance.



9036 Pocket knife

Item Number	
C9036	95mm 3 3/4"

Non-locking.

Trimming Knives

A range of professional quality trimming knives and blades.

Our knives are designed with the end-user in mind, with lots of tricks to make their job easier.





956 Trimming knife

Item Number	i
T0956-1	retractable blade
T0956-2	non-retractable blade

This knife features an interlocking body, magnetic blade holder, captive body screw, string cutting notch. Comes with ten free heavy duty C.K blades in a handy blade dispenser pack.



957 Soft-Grip Trimming knife

Item Number	i
T0957-1	retractable blade
T0957-2	non-retractable blade
M0957	trimming knife header card

This knife features an interlocking body, magnetic blade holder and a soft grip handle for greater comfort in use. Has a captive body screw retractable version has string cutting notch. Comes with ten free heavy duty C.K blades in a handy blade dispenser pack.



969 Safety knife

Item Number	i
T0969	safety knife

Blade retracts automatically when the lever is released thus reducing likelihood of injury. Ideal product for commercial use and within the home. Ergonomic, lightweight design with a matt finish for safer grip. Metal casing slightly covers blade giving greater protection. Simple blade change.



958 Trimming knife snap-off

Item Number	i
T0958	4 free blades

This knife features a soft grip handle for greater comfort and control in use, holds up to six blades and contains an integrated blade snapper. Supplied with four free blades.



959 Spare blades

Item Number			
T0959-10	60mm 2 ³ / ₈ "	0.6mm	10
T0959-50	60mm 2 ³ / ₈ "	0.6mm	50
T0959-100	60mm 2 ³ / ₈ "	0.6mm	100

Item Number	i
M0959	blade header card

Heavy duty blades supplied in a handy spring loaded blade dispenser for easy use.



971 Spare snap off blade

Item Number		
T0971-10	110mm 4 ⁵ / ₁₆ "	10

Ten heavy duty blades, each with eight segments, in a handy spring loaded dispenser.

Wood Chisels



1178 Bevelled Edge wood chisel

Item Number	
T1178 025	6mm 1/4"
T1178 037	10mm 3/8"
T1178 050	13mm 1/2"
T1178 062	16mm 5/8"
T1178 075	19mm 3/4"
T1178 087	22mm 7/8"
T1178 100	25mm 1"
T1178 125	32mm 1 1/4"
T1178 150	38mm 1 1/2"

Finely ground and sharpened, the chisels are ready for immediate use. They have tough shatter proof clear acetate handles and are supplied with protective end caps.



1126 Sharpening Stone

Item Number	
T1126	200 x 50mm

Medium/Fine silicon carbide sharpening stone, ideal for sharpening chisels, scissors, shears etc.

Our customers are currently enjoying:

- Same day despatch
- 98% stock availability
- 24 hour online ordering



1179 Wood Chisel display

Item Number	i	×
T1178LS	Stocked display stand	3 of each size
T1179L	empty display stand	
T1179H	header for display stand	

Contains 3 of each of all 9 sizes plus sharpening stone.



1180 Bevelled Edge wood chisel set

Item Number	i
T1180	wood chisel set

Set of 4 bevelled edge wood chisels (6, 13, 19 & 25mm) with shatterproof acetate handles for use with mallet or hammer. Supplied in durable, strong case with carry handle. Comes complete with a silicon carbide oil stone.

The hardened and tempered blades of the C.K wood chisel range means they can be resharpened down the entire blade length.

Files & Rasps



80 Engineers file

Item Number			
T0080 6		150mm 6"	95g
T0080 8		200mm 8"	186g
T0080 10		250mm 10"	344g

The flat, second cut file gives a moderate removal rate on most materials. One safe edge.



0080B Engineers file
bastard cut

Item Number			
T0080B 10		250mm 10"	312g

The flat, bastard cut file gives a high removal rate on most materials. One safe edge.

Files should never be used without a handle. This can lead to accidents and injuries.



0080S Engineers file smooth

Item Number			
T0080S 6		150mm 6"	101g
T0080S 8		200mm 8"	186g

The flat, smooth cut file gives a smooth surface finish on most materials. One safe edge.



82 Engineers file

Item Number			
T0082 6		150mm 6"	105g
T0082 8		200mm 8"	182g
T0082 10		250mm 10"	307g

The half round, second cut file is tapered toward the point and is used for filing concave and flat surfaces.

All our engineers files are fitted with a 'C.K Safety Handle'.



83 Engineers file

Item Number			
T0083 6		150mm 6"	63g
T0083 8		200mm 8"	115g
T0083 10		250mm 10"	206g

The round, second cut file, is tapered towards the point and is used for filing holes and concave surfaces.



72 Extra Slim saw file

Item Number			
T0072 5		125mm 5"	44g

Three sided.



73 Slim saw file

Item Number			
T0073 6		150mm 6"	99g

Three sided.



74 Standard saw file

Item Number			
T0074 6		150mm 6"	97g

Three sided.



75 Mill saw file

Item Number			
T0075 10		250mm 10"	240g

Second cut with one round edge.



79 Chain saw file

Item Number				
T0079 1		150mm 6"	4mm 5/32"	44g
T0079 2		200mm 8"	5mm 3/16"	62g
T0079 3		250mm 10"	5.5mm 7/32"	73g

Second cut, round file is tapered towards the point and is used for filing holes and concave surfaces.



106 Combined file and rasp

Item Number			
T0106 06		150mm 6"	108g
T0106 08		200mm 8"	216g

Hand, one side bastard rasp for wood, other coarse file cut for wood or metal.



107 Wood Rasp

Item Number			
T0107 06		150mm 6"	104g
T0107 08		200mm 8"	211g


Half round, bastard cut both sides for wood.

Each complete file is fitted with a 3 part handle designed to provide higher performance and comfort.

Shock absorbing inner plug effectively removes vibration from the thrust of the tang during use.

Strong solid core maintains the shape of the handle and prevents splitting.

Special, durable soft feel coating for comfort and maximum grip.



69 Safety file handle

Item Number			
T0069 1		fits 4 - 6"	1 25g
T0069 2		fits 6 - 10"	2 44g
T0069 3		fits 8 - 12"	3 61g

Designed for safety, performance and comfort. A softer exterior with a solid core and shock absorbing inner plug.



98 File Bar display

Item Number	i	×
T0098LS	complete display	6 of each files
T0098LS/1	complete display	3 of each files
T0098L	Empty file bar – no header	–
T0098H	Header for T0098L	–

contains

Item Number	i	↔
80	Engineer's file	150 & 200mm
80S	Engineer's file	150 & 200mm
82	Engineer's file	150 & 200mm
83	Engineer's file	150 & 200mm
106	File/Rasp	150 & 200mm
107	Wood Rasp	150 & 200mm
72	Extra slim saw file	125mm
73	Slim saw file	150mm
74	Standard saw file	150mm
75	Mill saw file	250mm
79	Chain saw file	150 & 200mm

Special file steel is used to manufacture our files. This is harder than standard steel so they last longer.



120 Warding file

Item Number	i	↔	🛒	×
T0120 1	🔪	100mm 4'	17g	6
T0120 2	🔪	100mm 4'	17g	6
T0120 3	🔪	100mm 4'	17g	6
T0120 4	🔪	100mm 4'	17g	6
T0120 5	🔪	100mm 4'	17g	6
T0120 6	🔪	100mm 4'	17g	6

Second cut with nickel plated ferrule and waxed wooden handles.



119 Warding file set

Item Number	i	↔	🛒
T0119	🔪🔪🔪🔪	100mm 4'	79g

Contains one of each 120 3-square, hand, round and tapered flat.



0120P Warding file set

Item Number	i	↔	🛒
T0120P	🔪🔪🔪🔪	100mm 4'	125g

Containing one of each 120 of all sizes.



0124P Needle files set of 6

Item Number	i	🛒	×
T0124P	🔪🔪🔪🔪🔪🔪	48g	6

Contains one of each of the following; Flat, Tapered Flat, Half Round, Round, Square and 3-Square.



71 Needle file handle

Item Number	↔	🛒
T0071	95mm 3¾"	20g

Ideal for the safe use of needle files, brass chuck and beech handle. Display packed.

Contact customer services on:

UK:
Tel: 01758 704 704 Fax: 01758 704 705
Email: sales@cki.uk.com

Republic of Ireland:
Tel: 1-800818 660 Fax: 1-800818 659
Email: dublin-sales@cki.uk.com

Rest of World:
Tel: +49 (0) 202 89030 Fax: +49 (0) 202 890322
Email: info@cki.de.com

Hammers



5701 Anti Vibration forged claw hammer

Item Number	🛒
357001	454g 16oz
357002	568g 20oz

Item Number	i
M0109	Highlighter - compatible with M0104 hammer hook

Single piece forged steel hammer for maximum strength and performance. Balanced weight design with energy saving claw geometry. Shock absorbing grip system.



All C.K hammers have drop forged and heat treated heads to prevent accidents caused by chipping or splitting. Designed to last, for light, heavy and specialist applications alike.



5702 Anti Vibration fibreglass shaft claw hammer

Item Number	
357003	454g 16oz
357004	568g 20oz

Item Number	
M0110	Highlighter - compatible with M0104 hammer hook

Strong fibreglass shaft for strength and performance. Balanced weight design with energy saving claw geometry. Shock absorbing contoured grip system for comfort and control.


All the C.K Anti Vibration hammers feature a shock absorbing grip system, which minimises the shock of impact and lessens the user's fatigue, enabling them to work efficiently for longer.



4203 Pin hammer

Item Number	
T4203	114g 4oz

The head is secured to an hickory handle by wooden and iron wedges. Suitable for knocking in small pins.



4229 Hi-Vis claw hammer

Item Number	
T4229 08	227g 8oz
T4229 16	454g 16oz
T4229 20	568g 20oz

Item Number	
M0112	Highlighter - compatible with M0104 hammer hook

Designed to stand out, this range of construction hammers feature a brightly coloured rubber grip which means the hammer is always visible.



4204 Joiners hammer (Warrington)

Item Number	
T4204 06	171g 6oz
T4204 08	227g 8oz
T4204 10	284g 10oz

The traditional Warrington Pattern is ideal for light woodwork assembly and general use. The Head is secured to an hickory handle by wooden and iron wedge.



4208 Engineers hammer

Item Number	
T4208H 08	1/2lb 227g
T4208H 16	1lb 454g
T4208H 24	1 1/2lb 681g
T4208H 32	2lb 908g

The traditional UK engineers hammer. The Head is secured to a top quality genuine hickory handle by wooden and iron wedges.



4227 Engineers hammer

DIN 1041

Item Number	
T4227A 0100	100g 3 1/2oz
T4227A 0200	200g 7oz
T4227A 0300	300g 10 1/2oz
T4227A 0500	500g 17 1/2oz
T4227A 1000	1000g 35oz

Manufactured to a German Pattern. The head is secured by ring wedge and epoxy resin. The ash handle as a grip section with a textured non-slip lacquer.



4225 Engineers hammer

Item Number	
356001	200g 7oz
356002	300g 10 1/2oz

Traditional French pattern. The head is secured by wooden and iron wedges.



5703 Anti Vibration Forged one-piece club hammer

Item Number	
357005	1361g 3lb

Item Number	
M0111	Highlighter - compatible with M0104 hammer hook

Single piece forged steel hammer for maximum strength and performance. Shock absorbing grip system.



4219 Club hammer

Item Number	
T4219 40	2 1/2lb 1135g
T4219 64	4lb 1816g

Traditional UK pattern. Genuine hickory handle.



4219A Club hammer

Item Number	
T4219A 10	2 1/4lb 1000g
T4219A 15	3 3/4lb 1500g

Manufactured to a German pattern DIN 6475. The ash handle is secured to the head by a ring wedge.



4218 Sledge hammer
fibreglass

Item Number	
T4218 40	8lb 3.63kg
T4218 64	12lb 5.44kg

A heavy, long handled version of the club hammer. Used mainly for building work. Both striking faces are precision ground, hardened & heat treated to help withstand the heavy applications. The 33" fibre-glass shaft has a rubber collar for overstrike protection.



4232 Brick hammer

Item Number	
T4232 16	16oz 454g
T4232 20	20oz 568g

Drop forged high carbon steel head, hardened and tempered. Keen, tough cutting edge with accurately ground and bevelled face. Chrome plated tubular steel shaft with C.K comfort rubber grip.



4234 Mortar Pick chisel point

Item Number	
T4234	chisel and point

The ideal tool for cleaning weathered and damaged mortar joints prior to repointing. The chrome plated tubular steel shaft has a comfort grip for greater ease.

Cold Chisels & Bolsters

Premium quality tools for cutting bricks & composite blocks, they are manufactured from premium grade steel and are hardened and tempered to BS 3066.

They are powder coated for extra corrosion resistance.



3086 Electricians bolster chisel

Item Number			
T3086	225mm 8 3/4"	55mm 2 1/4"	
T3086S	225mm 8 3/4"	55mm 2 1/4"	with grip

A versatile tool for lifting floorboards and chasing plaster. Ideal for electrical and plumbing installation work. Ideally sized for chasing patress boxes. T3086S comes with an impact absorbing, protective rubber grip. Length 225mm / 8 3/4".



3087 Brick bolster chisel

Item Number			
T3087 3	230mm 9"	75mm 3"	
T3087 4	230mm 9"	100mm 4"	
T3087S 3	230mm 9"	75mm 3"	with grip
T3087S 4	230mm 9"	100mm 4"	with grip

Specifically designed for cutting bricks and composite blocks during building work. T3087S comes with an impact absorbing, protective rubber grip. Length 230mm / 9".



3088 Plugging chisel

Item Number		
T3088	250mm 10"	25mm 1"

A chisel with an angled and grooved cutting edge, designed for the effective removal of mortar and cement from between bricks and block work.

C.K cold chisels can also be used for cutting soft steel sections.



3383 Cold chisel

Item Number		
T3383 06	150mm 6"	12mm 1/2"
T3383 07	180mm 7"	16mm 5/8"
T3383 08	200mm 8"	19mm 3/4"
T3383 10	250mm 10"	19mm 3/4"
T3383 101	250mm 10"	25mm 1"
T3383 12	300mm 12"	25mm 1"
T3383 18	460mm 18"	19mm 3/4"

Mainly designed for cutting small section steel, these chisels can also be used on brick and concrete.


Scutch chisels were traditionally used for dressing stone, but they are commonly used for neat chasing into finished wall surfaces.



3091 Scutch chisel

Item Number	
406001	25mm 1"
406002	32mm 1 1/2"

Supplied complete with comb bit.



4211 Spare comb / chisel bits

Item Number		
T4211/1	25mm 1"	scutch combs
T4211/2	25mm 1"	scutch droves
T4211/3	38mm 1 1/2"	scutch combs
T4211/4	38mm 1 1/2"	scutch droves

Wallet of 10 spare comb or drove bits for the scutch chisels.

Trowel/Float



5293 Brick trowel
Philadelphia pattern

Item Number	
T529311	280mm 11"

High carbon steel blade welded to heavy duty tang for strength & durability.



5295 Brick trowel
Broad heel

Item Number	
T529510	255mm 10"



5296 Pointing trowel

Item Number	
T529606	150mm 6"

Unique asymmetric shape, one curved edge and one straight for intricate, fine finishing.

Our soft-grip handle has a patented finger guard.



5292 Gauging trowel

Item Number	
T529207	180mm 7"



5297 Finger & Jointing trowel

Item Number	
T529750	175 x 13mm 7" x 1/2"



5271 Brick trowel
Philadelphia pattern

Item Number	
T527111	275mm 11"

Forged tang welded to hardened & tempered blade. Half tanged to hardwood handle.

Order Online

www.carlkammerling.com



5270 Brick trowel
Broad heel

Item Number	
T527010	250mm 10"
T527011	275mm 11"



5060 Pointing trowel

Item Number	
T5060 4	100mm 4"
T5060 5	125mm 5"
T5060 6	150mm 6"



5272 Gauging trowel

Item Number	
T527207	175mm 7"

C.K welded blade and tang assembly has been tested against UK market leading fully forged trowels, and found to be stronger in independent VPA tests.



5073 Finger trowel

Item Number		
T5073 37	175mm 7"	10mm 3/8"
T5073 50		13mm 1/2"
T5073 62		16mm 5/8"
T5073 75		19mm 3/4"
T5073 99		25mm 1"
T5073 1		13mm 1/2"

T5073 1 with half round blade. Display packed.



5273 Margin trowel

Item Number		
T5273	125mm 5"	margin trowel

Parallel edges for borders & working in confined spaces

Our hardened and tempered steel bladed building trowels have taper ground blades, which gives them the ideal balance of strength and flexibility.



5241 Brick trowel
Philadelphia pattern – stainless steel

Item Number	
T524111	280mm 11"

Stainless steel, non-marking blade. Will not rust.

We have a range of stainless steel building trowels which are ideal for infrequent use since they will not rust.



5243 Pointing trowel stainless steel

Item Number	
T524306	150mm 6"



5242 Gauging trowel stainless steel

Item Number	
T524207	175mm 7"



5198 Brick jointer

Item Number	
T5198	13 x 16mm 1/2 x 5/8"

Fully hardened & tempered carbon steel. For finishing 13mm (1/2) & 16mm (5/8) mortar joints.



5093 Trowel & Square tool

Item Number	
T5093 50	265mm 10 1/2" 13mm 1/2"
T5093 62	265mm 10 1/2" 16mm 5/8"

Trowel blade, hardened, tempered and ground to give correct flexibility and balance.



5298 Finishing trowel

Item Number	
T5298	280 x 120mm 11 x 4 3/4"

Professional quality, lightweight plasterers trowel with carbon steel blade. Tang securely fastened by spot welded pins. Soft grip, banana shaped handle.



5068 Finishing trowel

Item Number	
T5068	280 x 120mm 11 x 4 3/4"

Top quality. Extra thin (0.65mm/23 B.W.G.) flexible, polished blade. Handle mounting is securely fastened by spot welded pins. Steel is tanged through poplar wood handle to fixing nut.


Stainless Steel finishing trowels are ideal for dry walling, as they don't mark the dry wall with rust deposits.



5072 Finishing trowel stainless steel

Item Number	
T5072	280 x 120mm 11 x 4 3/4"

Stainless steel, top quality trowel. Specification as T5068 but with thinner (0.6mm) Stainless Swedish steel blade.



5299 Finishing trowel stainless steel

Item Number	
T5299	330 x 120mm 13 x 4 3/4"

Extra large stainless steel finishing trowel with traditional, banana shaped wooden handle.



5069 Plasterer's hawk

Item Number	
T5069	300 x 300mm 12 x 12"

Aluminium blade with grooved, non-slip surface. Detachable plastic handle.



5264 Flooring trowel

Item Number	
T5264	405 x 115mm 16 x 4 1/2"

Pointed, carbon steel blade flooring trowel for easy access into corners. Wooden handle with double hang tang for balance in use. Used for applying & finishing concrete or cement floors.



5274 Concrete Edging trowel

Item Number	
T5274	280 x 115mm 11 x 4 1/2"

Edging trowel with long curved edge, suitable for rounding off concrete corners. Steel blade with wooden handle securely fastened by 6 rivets.



T5169 1 T5169 2

5169 Adhesive trowel

Item Number	
T5169 1	255 x 115mm 10 3/4 x 4 1/2"
T5169 2	255 x 115mm 10 3/4 x 4 1/2"

Polished carbon steel blade with welded polypropylene handle. Broad round profile notches, ideal for applying adhesive for floor tiles. T5169 2 with small round profile notches.



5172 Skimmer float

Item Number	
T5172	280 x 140mm
T5172 18	320 x 180mm

Lightweight, moulded foam plastic with fine chequered working face. Durable and non-warping. Available in 2 sizes.



5174 Grouting float

Item Number	
T5174	280 x 140mm 11 x 5 1/2"

Lightweight, durable handle bonded to dense rubber pad. Suitable for grout application.



5173 Grout sponge

Item Number	
T5173	280 x 140mm 11 x 5 1/2"

Lightweight, backing of moulded foam plastic with 20mm thick general purpose sponge face, suitable for washing down grout.



5097 Harling trowel

Item Number	
T5097	165 x 165mm 6 1/2 x 6 1/2"

Heavy grade steel and ferruled hardwood handle. Ideal for pebble dashing and similar surface finishes.

Scraping & Filling tools



5070 Painters scraper and filling knife

Item Number			
T5070A 040	40mm 1 1/2"		painter's scraper
T5070A 050	50mm 2"		
T5070A 070	70mm 2 3/4"		
T5070A 100	100mm 4"		

Manufactured from taper ground, high quality, spring steel. Strong blade for scraping yet flexible enough for filling too. Plastic handle with hanging hole.



5070 Painters scraper and filling knife display

Item Number	
T5070A/4LS	304 x 300 x 140mm

Compact display unit for either counter or toolbar display.



5075 Painters scraper

Item Number			
T5075 1	25mm 1"		painter's scraper
T5075 2	50mm 2"		
T5075 3	75mm 3"		
T5075 4	100mm 4"		

This painter's scraper is designed to last, the taper ground spring steel gives strength and flexibility, and the rosewood handle is extremely durable.



5077 Filling knife

Item Number			
T5077 3	75mm 3"		filling knife

This filling knife is the ideal tool manufactured similarly to T5075 but with a more flexible blade for filling.



5076 Putty knife

Item Number	
T5076	putty knife

Designed with a clip point suitable for shaping and smoothing putty once the window glass is in place.



5064 Superflex scraper

Item Number	
T5064	scraper set

Set of 4 super flexible scrapers. Ideal for delicate jobs and general DIY use e.g. removing paint from glass, filling, etc. Supplied in four widths 50, 80, 100 and 120mm with plastic hand guard. Made in Germany.

Riveting tools



3820 Hand Riveting plier

Item Number			
T3820	260mm 10 1/2"		riveting pliers
T3820AS	300mm 12"		riveting plier kits

Designed for use with aluminum and steel rivets up to 4.8mm (3/16). Comes supplied with 3 colour coded interchangeable nose bushes to accept 3.15mm (1/8), 4mm (5/32), 4.8mm (3/16) rivets. The bushes are colour coded to aid correct rivet selection when using C.K rivets. Display packed. Kit contains: Hand riveting pliers, 25 each of rivets, 3.15mm (1/8) short, 4mm (5/32) short and 4.8mm (3/16) medium. All contained in a tough, durable plastic storage case.

C.K hand riveting pliers have 3 jaws instead of the usual 2. This means: - the plier grips the rivet better, meaning less slippage - the jaws have a longer life due to less wearing - force is applied evenly over the rivet avoiding breakage of the inner tube. The C.K three jaw riveter is 50% stronger than a two jaw equivalent.



3819A Aluminium rivets

Item Number			i	×
T3819A 408	3.15 X 6mm	1/8 x 1/4"	short	50
T3819A 412	3.15 x 9mm	1/8 x 3/8"	medium	50
T3819A 415	3.15 x 12mm	1/8 x 1/2"	long	50
T3819A 508	4 x 6mm	5/32 x 1/4"	short	50
T3819A 512	4 x 9mm	5/32 x 3/8"	medium	50
T3819A 515	4 x 12mm	5/32 x 1/2"	long	50
T3819A 612	4.8 x 9mm	3/16 x 3/8"	medium	50
T3819A 615	4.8 x 12mm	3/16 x 1/2"	long	50
T3819A 620	4.8 x 16mm	3/16 x 5/8"	extra long	50

Rivets made from aluminium. Packed in 50's a in sturdy storage box. (4.8mm in 40's).



3824 Washers

Item Number		×
T3824 12	3.15mm 1/8"	100
T3824 15	4mm 5/32"	100
T3824 18	4.8mm 3/16"	100

For use with C.K Rivets. Sizes given are internal diameter.

The stems of C.K rivets are colour coded to match the nose bushes of the riveting pliers for ease of selection and correct usage.



3822 Lazy Tong riveter

Item Number	
T3822A	780mm 32 1/2"

Designed with ANTI-SHOCK built-in to protect the user against an injury to wrists, elbows or shoulders. For use with aluminium and steel rivets 2.4, 3.15, 4.0, 4.8 and 6.0mm.



3825 Riveting display stand

Item Number	i	
T3825LS	complete rivet plier display	570 x 530 x 330mm
T3825L	empty stand	
T3825H	header for empty stand	

contains

Item Number	i		×
T3820	riveting pliers		3
T3820AS	riveting pliers sets		3
T3819A	aluminium rivets (boxed)	all 9 sizes	6
T3824	washers (boxed)	all 3 sizes	6

Stapling & Adhesives

Our staple and cable tacking guns all have an ingenious staple loading and clearing mechanism.



6222 Heavy duty staple gun

Item Number	i
496001	heavy duty staple gun

A heavy duty staple gun featuring a tough die cast aluminium body, bi-material ergonomic handle with safety locking system. Fires staples 6-14mm (interchangeable with Arrow T50 or Rapid 140 6-14mm) and nails (brads) 18 gauge 16mm. Supplied complete with approximately 200 x 8mm staples.

6223 Staples

Item Number		
496002	8mm	10.5mm
496003	10mm	
496004	12mm	
496005	14mm	

Spare staples with 10.5mm crown width. Display packed.



6225 Cable tacker
low voltage cable

Item Number	
T6227	6.4mm 1/4"

A heavy duty cable tacker featuring a tough die cast aluminium body, bi-material ergonomic handle with safety locking system. Fires half round staples for use on low voltage cable (maximum diameter 6.4mm) (interchangeable with Arrow T25).

6225 Staples
for low voltage cable

Item Number	
495021	10mm
495022	14mm



6226 Cable tacker
telecom cable

Item Number	
T6228	4.5mm

As per T6227 but for telecom cable (maximum diameter 4.5mm).

6226 Staples
for telecom cable

Item Number	
495024	10mm



6222 Stocked stapler stand

Item Number	
T6222LS	stocked stapler stand
T6222H	header for stand
T6222L	empty stapler stand



6224 Stocked cable tacker
stand

Item Number	
T6224LS	stocked cable tacker stand
T6224H	header for stand



6215 Glue guns

BS6125

Item Number		
T6215	glue gun	3 pin plug
T6215A	glue gun	2 pin plug

Professional quality glue gun with 80W heater, ensuring fast heating and improved glue flow. 230V mains supply, fitted with a BS certified moulded plug, CE approved. Moulded trigger advance allowing greater application control. Safety heat insulated nozzle. Detachable wire stand. Maximum glue output is 21g / minute. Supplied complete with two 100mm long x 11mm diameter all purpose glue sticks.



6216 Glue gun kit

Item Number		
T6216	glue gun kit	2 pin plug

Kit contains T6215A and 12 200mm glue sticks in a carrying case.



6218 Glue sticks – all purpose

Item Number		
T6218 06	100mm	6
T6218 25	100mm	25

6219 Glue sticks

Item Number		
T6219 025	200mm	25
T6219 125	200mm	125

Our customers are currently enjoying:

- Same day despatch
- 98% stock availability
- 24 hour online ordering



Soldering Tools



950 Soldering iron

Item Number		
495009	soldering iron 25W	3-pin plug
495010	soldering iron 40W	3-pin plug
495011	soldering iron 25W	2-pin plug
495012	soldering iron 40W	2-pin plug
495013	spare tip set for 25W	–
495014	spare tip set for 40W	–

240V Heavy duty construction. VDE and GS certified long life tips – suitable for use with lead free solder. Replacement tip sets for C.K soldering irons contain one pointed and one chisel end.



6103 Desoldering tool

Item Number		
T6103	desoldering tool	210mm 8 1/4"

High capacity pump with 14.5cm³ volume. Body made from antistatic high quality glass fibre reinforced nylon. Heat resistant & conductive carbon fibre tip. Spring pressure can be increased or decreased by turning the spring around. Length incl. tip 210mm / 8. 1/4" Ø 26mm / 1".



6104 Carbon spare nozzles

Item Number	
T6104	spare nozzles

Heat resistant conductive carbon fibre spare tip for T6103.



1881/2 Power mixer

Item Number		
T1881	420mm	16 1/2"
T1882	620mm	25"

Manufactured from nickel plated steel. Suitable for use with electric drills at speeds between 200 - 700 rpm depending on the material being mixed. Ideal for mixing paint, paste, adhesive, cement, screed, filling compounds, etc.



4310 Prybar/Nail puller/scrapper

Item Number		
T4310	380mm	15"

The angle ground ends can also be used as a scraper.



4314 Wrecking bar

Item Number		
T431418	455mm	18"
T431424	610mm	24"

Goose neck wrecking bars for heavy duty tasks such as levering timber and pulling nails.



5180 Slater's ripper

Item Number		
T5180		slater ripper


Used for shearing off fixing nails prior to the replacement of damaged slates.



5081 One Handed suction lifter

Item Number		
T5081	120mm	4 3/4"
		30Kg

With one handed action, this lifter attaches when the handles are squeezed together and the suction is activated. Useful for lifting and transporting glass panes, coated wooden boards, metal panels, marble, ceramics and other heavy, bulky items with smooth, non-porous surfaces. The heavy duty body is made of shock resistant plastic and the cups are made of natural rubber.



5082 One Handed suction lifter

Item Number		
T5082	320mm	12 3/4"
		60Kg

Lifted by one hand but with two lever operated suction pads, this tool is ideal for lifting and positioning heavier items such as refrigerators, large glass sheets and other awkward objects. For heavier items two or more Double Suction Lifters can be used together. The heavy duty body is made of shock resistant plastic and the cups are made of natural rubber.



5087 Glass cutter

Item Number		
T5087		glass cutter

Professional quality glass cutter. 6 top quality wheels in turret head. Oiled felt washer for lubrication. Heavy nickel plated head. Lacquered handle.



50010 Tie Gun for cable binder

Item Number		
495003		2.4mm - 4.8mm

Body constructed from strong yet lightweight reinforced glass fibre. The binding tension can be adjusted using the tension adjuster. Automatic cut off - pull the trigger and the tie is automatically tensioned and cut.



50020 Tie Gun for cable binder

Item Number		
495004		4.7mm - 13mm

Designed for heavy duty use. The red lacquered stainless steel body protects against corrosion. The tension adjuster gives a secure binding automatic cut off - pull the trigger and the tie is automatically tensioned and cut.



5390 Draw tape

Item Number		
495005		10m
495006		20m
495007		30m

For drawing electrical wiring through conduits and trunking etc. The 190mm spring guide avoids jamming. Extra strong perlon tape for performance and reliability. The smooth surface offers low friction. Non-conductive and non-corroding. 4mm Ø.



5391 Electrician's fish tape

Item Number		
495008		50ft / 15.2m

For drawing electrical wiring through conduit. Manufactured from high strength flexible spring steel with a hooked end to avoid snagging in use. Housed in a sturdy rotating plastic storage case with brake trigger mechanism in handle.



2378 Punch Down tool

Item Number		
495033		180mm 7"

For seating Telecom and data cables into terminals - automatically trims excess wires during punch down action. Suitable for a wide range of terminal blocks, including KRONE and similar. The handle includes wire extractor hook and spudger.



4041 Re-Threading tool

Item Number		
495028	M3.5	0.6
495029	M4	0.7



6238 Wire brush

Item Number	
T6238 4	4 rows

Top quality oil hardened and tempered steel wire bristles of 25mm (1") length. Solid waxed beech stock with hanging hole. Length 295mm / 11¾", Working length 140mm / 5½".



5912 Inspection mirror

Item Number		Ø
T5912 38	125 - 685mm	38mm
T5912 55	125 - 560mm	55mm

Telescopic inspection mirror with swivel head and pocket clip.



5913 Inspection mirror

Item Number		Ø
T5913 32	180 - 520mm	32mm

Telescopic inspection mirror with swivel head and pocket clip.



5914 Inspection mirror

Item Number		Ø
T5914 55	250 - 780mm	55mm

Telescopic inspection mirror with swivel head.



5901 Inspection lamp

Item Number	
T5901	U.K 3-pin
T5901A	Euro 2-pin

Heavy duty steel cage and glass. Screw bulb holder. Heavy rubber grip and suspension hook. Supplied with 5m of 2 core cable and plug. Max 60W bulb (not included). Sold loose.



5902 Inspection light

Item Number	
T5902	U.K 3-pin
T5902A	Euro 2-pin

Fluorescent 240V, 8 watt lamp. Supplied with 5m of 2 core resistance cable and plug.



6270 Grease Gun High Pressure

Item Number	
T6270	500cm³

Heavy duty construction with pressure head. Multiple loading: cartridge, grease gun filler or bulk. Precision machined piston and pump cylinder. Air release valve. Wide safety knurls provide a sure grip. Supplied complete with angles delivery tube and 4 jaw hydraulic coupler. Delivery pressure 400/5800 psi. Capacity 500cm³ / 17½ft oz.

6270 Grease Gun accessories

Item Number		i
T6270 2	300mm	flexible hose
T6270 3	450mm	flexible hose
T6270 4	–	coupler
T6270 5	–	grease cartridge



6283 Graphite lubricant

Item Number	
T6283A	50g

50g microfine, greaseless and odourless. Suitable for car door locks and outside padlocks as being dry, it cannot freeze.



3328 Parallel pin punch

Item Number	Ø		×
T3328 05	2mm 5/64"	150mm 6"	1
T3328 06	2.5mm 3/32"		1
T3328 08	3mm 1/8"		1
T3328 10	4mm 5/32"		1
T3328 12	5mm 3/16"		1
T3328 14	5.5mm 7/32"		1
T3328 16	6mm 1/4"		1
T3328 20	8mm 5/16"		1
T3328 24	10mm 3/8"		1
T3328S	2, 2.5, 3, 4, 5, 6mm		6



4032 Tap & Die set

Item Number	i
T4032	tap and die set

21 piece metric tap & die set in a plastic storage case with transparent cover. Components are manufactured from high carbon steel, hardened & tempered. Display packed. Containing 1 each: Tap & Dies Sizes: 3, 4, 5, 6, 7, 8, 10, 12mm 0.5, 0.7, 0.8, 1.0, 1.25, 1.5, 1.75 pitch mm

Tap & Die: 1/8" NPT. Bar type tap wrench: M3-12 (1/8"-1/2"). Die holder. Screwdriver Metric tap & die set suitable for forming internal & external threads in soft material. Can also be used for removing rust & flaking paint from existing threads.



3062 Screw extractor set

Item Number		i
T3062 01	1, 2, 3, 4, 5	5 piece
T3062 02	1, 2, 3, 4, 5, 6	6 piece

Manufactured in Germany from chrome vanadium steel with square drive ends. With left hand thread for extracting broken studs and screws.