

BP880 BNC to Female Double Stacking Banana Plug



Overview

Converts a BNC scope lead to a dual banana plug for connection to a DMM. Required when adapting a shielded BNC cable, found on high-end low current clamps such as the Fluke 80i-110s, to a DMM.

- Allows for hands-free testing in controlled voltage environments 500 VRMS maximum.
- Banana plug is nickel-plated, beryllium copper for low contact resistance
- The BNC shell is plated for tarnish resistance
- Operating temperature +50 °C (+122 °F) maximum