

SERIES 29

FEATURES

- Quick Connect/Disconnect
- Only $\frac{7}{8}$ " Above Board Height
- Standard, Insulated, or Banana Plug Styles
- High Temperature Spring Style
- Color-Coded Caps with Optional Additional Colors




DESCRIPTION

Press button and put lead in slot and release. Spring pressure assures firm, positive contact.

DIMENSIONS In Inches (and millimeters)

Standard Style




Red/Black cap **Part No. 29-100**

No cap **Part No. 29-110**


No cap, high temp. **Part No. 29-125**

Insulated Style



Same as 29-100 with Black Thermoset Plastic Washers **Part No. 29-104**

Banana Plug Style



Fits Standard Banana Socket **Part No. 29-101**

SPECIFICATIONS

Rating Criteria

Rating: At 120 Vdc, 20A continuously, with a maximum temperature rise of 20°C.

Materials and Finishes

External Metal Parts: Nickel-plated brass

Spring: Tinned music wire

Button Caps: Polyethylene

Washers (29-104): Black thermoset plastic

High Temperature Spring: Stainless steel

OPTIONS

Green or White Caps

Gold plate finish: Available on all but Banana Plug styles.

ORDERING INFORMATION

Description	Part Number
Standard, without cap	29-110
Standard, with red cap	29-100 RED
Standard, with black cap	29-100 BLK
High temperature standard, without cap	29-125
Insulated, with black cap	29-104 BLK
Insulated, with red cap	29-104 RED
Banana plug, with black cap	29-101 BLK
Banana plug, with red cap	29-101 RED

Available from your local Grayhill Distributor.

For prices and discounts, contact a local Sales Office, an authorized local Distributor or Grayhill.