



FEATURES:

- Provides a fast and easy method to splice two cables together to increase cable length.

MATERIALS:

Jacks : Brass, Nickel Plated

Insulation: Polypropylene

RATINGS:

Operating Voltage: 5000 VDC

Operating Temperature: +55° C. (+131° F.) Max.

Current: 15 Amperes Max.

ORDERING INFORMATION: Model 1829-*

* = Color, Standard Colors: -0 Black, -2 Red

Sold in packages of ten.

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

1829-0 1829-2